ABB BALDOR RELIANCE

Customer information packet

AOM3556T

1HP, 1170RPM, 3PH, 60HZ, 145T, 3526M, TEAO, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 2:08:19 AM

Specifications

Enclosure	TEAO
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ
	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.600 A @ 208.0 V
	3.560 A @ 230.0 V
	1.780 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	F
Type	AC
Mech. spec.	35K695
Base	
Status	PRD/A
Elec. spec.	35WGG330
Layout	35LYK695
Eff. date	01-14-2026
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	09-09-2022

High Voltage Full Load Amps	1.8 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	12.12 IN
Power Factor	64
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	AOM3556T								
SPEC.	35K695G330G1								
HP	1								
VOLTS	208-230/460								
AMP	3.6-3.56/1.78								
RPM	1170								
FRAME	145T	**HZ**	60			**PH**	3		
SER.F.	1.00	**CODE**	K	**DES**	B	**CLASS**	F		
NEMA-NOM-EFF	82.5	**PF**	64						
RATING	40C AMB-CONT								
CC									
DE	6205	**ODE**	6203						
ENCL	TEAO	**SN**							

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data
Record # 87635
Typical performance - not guaranteed values

Winding: 35WGG330-R002	**Type:** 3526M	**Enclosure:** TEAO

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	4.47 LB-FT
Volts			208-230/460	**Start Configuration**	direct on line
Full Load Amps			3.6-3.56/1.78	**Breakdown Torque**	13.22 LB-FT
R.P.M.			1170	**Pull-up Torque**	7.94 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	9.7 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	10.19 A
Service Factor (S.F.)			1	**No-load Current**	1.19 A
NEMA Nom. Eff.	82.5	**Power Factor**	64	**Line-line Res. @ 25ºC**	19.9 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	48°C
				Locked-rotor Power Factor	50.1
				Rotor inertia	0.189 lb-ft²

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	27	43	55	64	70	73
Efficiency	70.2	80.1	82.3	82.5	81.5	79.4
Speed	1193	1187	1180	1172	1163	1153
Line amperes	1.23	1.36	1.54	1.78	2.06	2.41


ABB Motors and Mechanical Inc.


WINDING # 35WGG330

1 HP 3 PH 60 HZ 1170 RPM 460 V 3526M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=13.22 PU=7.94 LR=9.7 LRA=10.19




35LYK695
510-520 = 11.12
521-528 = 12.12
529-535 = 13.00
536-546 = 14.37
GREASE FITTINGS EACH END
2.50
2.25
NAMEPLATE
.19 KEY
1.38 LONG
2.59
Ø .8750
.8745
6 HOLES
Ø.38
4.00
2.25
5.00
.50
5.94
Ø 6.61
5.75
7.05
3.50
3.44
LEAD HOLE
Ø.88
2.75
2.75
4.63
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOADING OF SWD DWG FOR 2D TO 3D CONVERSION - PKG16
REV: G
VERSION: 04
REVISED: 04:48:21 02/01/2019
TDR: 000001098202
MODEL NO. 35LYK695
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
HORZ 35M 143-5T TEAO W/LOCKED PU BRG
SH 1 OF 1
35LYK695

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS