ABB BALDOR RELIANCE

Customer information packet

AOM3704T

3 AIR OVERHP, 1150RPM, 3PH, 60HZ, 213T, 3720M
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 3:15:58 AM

Specifications

Enclosure	TEAO
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ
	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.100 A @ 460.0 V
	10.200 A @ 230.0 V
	10.100 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	C
Type	AC
Mech. spec.	37F359
Base	
Status	PRD/A
Elec. spec.	37WGL950
Layout	37LYF359
Eff. date	10-09-2025
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	03-21-2023

High Voltage Full Load Amps	5.1 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3720M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	16.32 IN
Power Factor	66
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1150 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	AOM3704T								
SPEC.	37F359L950G1								
HP	3 AIR OVER								
VOLTS	208-230/460								
AMP	10.1-10.2/5.1								
RPM	1150								
FRAME	213T	**HZ**	60			**PH**	3		
SER.F.	1.00	**CODE**	J	**DES**	B	**CLASS**	F		
NEMA-NOM-EFF	84	**PF**	66						
RATING	40C AMB-CONT								
CC									
DE	6307	**ODE**	6206						
ENCL	TEAO	**SN**							
	1275 FPM AT 170CFM								

Accessories

Part number	Description	Multiplier
37-3301	C FACE KIT	P1

AC Induction Motor Performance Data
Record # 99001
Typical performance - not guaranteed values


Winding: 37WGL950-R001	**Type:** 3720M	**Enclosure:** TEAO

Nameplate Data			
Rated Output (HP)			3 AIR OVER
Volts			208-230/460
Full Load Amps			10.1-10.2/5.1
R.P.M.			1150
Hz	60	**Phase**	3
NEMA Design Code	B	**KVA Code**	J
Service Factor (S.F.)			1
NEMA Nom. Eff.	84	**Power Factor**	66
Rating - Duty			40C AMB-CONT

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	13.63 LB-FT
Start Configuration	direct on line
Breakdown Torque	39.8 LB-FT
Pull-up Torque	22.8 LB-FT
Locked-rotor Torque	28 LB-FT
Starting Current	26.8 A
No-load Current	3.25 A
Line-line Res. @ 25ºC	4.44 Ω
Temp. Rise @ Rated Load	38°C
Locked-rotor Power Factor	29.7
Rotor inertia	0.497 lb-ft²

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	28	45	58	66	71	74
Efficiency	74.7	82.4	84.5	83.9	82.2	80.4
Speed	1186	1175	1163	1149	1134	1115
Line amperes	3.39	3.75	4.32	5.07	6.01	7.07


ABB Motors and Mechanical Inc.
WINDING # 37WGL950
3 HP 3 PH 60 HZ 1150 RPM 460 V 3720M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=39.8 PU=22.8 LR=28 LRA=26.8
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (3 HP)
11/3/2026 ACPERF, record # 99001

AC Induction Motor Performance Data
Record # 99002
Typical performance - not guaranteed values

Winding: 37WGL950-R001	**Type:** 3720M	**Enclosure:** TEAO

Nameplate Data				**208 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			3 AIR OVER	**Full Load Torque**	13.74 LB-FT
Volts			208-230/460	**Start Configuration**	direct on line
Full Load Amps			10.1-10.2/5.1	**Breakdown Torque**	31.8 LB-FT
R.P.M.			1150	**Pull-up Torque**	17.4 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	21.4 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	46.3 A
Service Factor (S.F.)			1	**No-load Current**	5.04 A
NEMA Nom. Eff.	84	**Power Factor**	66	**Line-line Res. @ 25ºC**	1.11 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	38°C
				Locked-rotor Power Factor	29.7
				Rotor inertia	0.497 lb-ft²

Load Characteristics 208 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	36	56	68	73	76	75
Efficiency	79.1	84.8	85.6	84	81	77.4
Speed	1184	1172	1157	1140	1119	1088
Line amperes	5.46	6.52	8.09	10.08	12.63	15.97


ABB Motors and Mechanical Inc.


WINDING # 37WGL950

3 HP 3 PH 60 HZ 1150 RPM 208 V 3720M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=31.8 PU=17.4 LR=21.4 LRA=46.3




37LYF359
(717-735) = 16.32
(736-744) = 17.45
(745-750) = 18.20
(751-756) = 18.95
3.44
3.88
3.38
GREASE FITTING
(EA. END)
NAMEPLATE
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
9.58
7.96
2.26
10.02
5.25
5.19
LEAD
HOLE
Ø1.09
4.25
4.25
6.72
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: H
VERSION: 02
REVISED: 09:49:34 10/11/2022
TDR: 000001197758
MODEL NO. 37LYF359
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ 213-5T TENV 37M W/LOCKED BRG
37LYF359

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS