

ABB BALDOR RELIANCE III

Customer information packet

BM3568

.25HP, 1725RPM, 3PH, 60HZ, 56, BRAKE, 3413M

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.250 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Brake Torque	3.0 lb-ft
Current @ Voltage	1.000 A @ 230.0 V .950 A @ 208.0 V .500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Brake Mounting

Part Detail

Revision	V
Type	AC
Mech. spec.	34K044
Base	
Status	INA/A
Elec. spec.	34WG0139
Layout	34LYK044
Eff. date	09-26-2016
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-01-0001

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3413M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.36 IN
Power Factor	66
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Nameplate

NP1256L											
CAT.NO.	BM3568										
SPEC.	34K44-139-B										
HP	.25										
VOLTS	208-230/460										
AMP	.95-1/.5										
RPM	1725										
FRAME	56		HZ	60				PH	3		
SER.F.	1.00		CODE	K	DES	B		CLASS		B	
NEMA-NOM-EFF	68		PF	66							
RATING	40C AMB-CONT										
CC											
DE	6203		ODE	6203							
ENCL	TENV		SN								

AC Induction Motor Performance Data

Record # 6548

Typical performance - not guaranteed values

Winding: 34WG0139-R001			Type: 3413M		Enclosure: TENV	
Nameplate Data				460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		.25		Full Load Torque		0.75 LB-FT
Volts		208-230/460		Start Configuration		direct on line
Full Load Amps		0.95-1/.5		Breakdown Torque		3.1 LB-FT
R.P.M.		1725		Pull-up Torque		2.4 LB-FT
Hz	60	Phase	3	Locked-rotor Torque		2.5 LB-FT
NEMA Design Code		B	KVA Code	Starting Current		3 A
Service Factor (S.F.)		1		No-load Current		0.38 A
NEMA Nom. Eff.		68	Power Factor	Line-line Res. @ 25°C		60.4 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		36°C

Load Characteristics 460 V, 60 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	32	45	56	65	72	77
Efficiency	48	63.4	70.3	73.7	75.3	75.8
Speed	1781	1768	1753	1738	1722	1704
Line amperes	0.39	0.41	0.44	0.49	0.54	0.6

ABB Motors and Mechanical Inc.

WINDING # 34WG0139

Typical performance - not guaranteed values.

0.25 HP 3 PH 60 HZ 1725 RPM 460 V 3413M

TORQUES (LB-FT) : PO=3.1 PU=2.4 LR=2.5 LRA=3





