

ABB BALDOR RELIANCE III

Customer information packet

CBM7010

.75HP, 1750RPM, 3PH, 60HZ, 56C, 3514M, XPNV, F1

Class - CLI GP D

Division - Division I

Specifications

Enclosure	XPNV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.140 A @ 460.0 V 2.280 A @ 230.0 V 2.400 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T2C
Heater Indicator	No Heater

Part Detail

Revision	F
Type	AC
Mech. spec.	35E713
Base	
Status	PRD/A
Elec. spec.	35WGG069
Layout	35LYE713
Eff. date	04-02-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

High Voltage Full Load Amps	1.1 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3514M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.13 IN
Power Factor	74
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0015XPSL									
NO.		CC							
SER. #									
SPEC	35E713G069G1								
CAT.NO.									
H.P.	.75		T. CODE	T2C					
VOLTS	230/460								
AMPS	2.4/1.2								
R.P.M.	1765								
HZ	60		PH	3		CLASS	F		
SER.F.	1.00		DES	B		CODE	K		
RATING	40C AMB-CONT								
FRAME	56C					NEMA NOM. EFF	82.5		
		PF	74						
BLANK	SFA 2.68/1.34								

AC Induction Motor Performance Data

Record # 87322

Typical performance - not guaranteed values

Winding: 35WGG069-R009			Type: 3514M		Enclosure: TENV		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.75	Full Load Torque		2.24 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		2.42/2.42	Breakdown Torque		8 LB-FT		
R.P.M.		1765	Pull-up Torque		4.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		5.1 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		8.4 A
Service Factor (S.F.)		1.25	No-load Current		0.85 A		
NEMA Nom. Eff.		82.5	Power Factor	74	Line-line Res. @ 25°C		30.3 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		75°C
S.F. Amps		2.8/1.4	Temp. Rise @ S.F. Load		94°C		
			Locked-rotor Power Factor		66.8		
			Rotor inertia		0.101 lb-ft²		

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	48	61	70	77	81	80
Efficiency	68.4	79	82.2	82.9	82.4	81.2	82.8
Speed	1791	1783	1775	1766	1757	1746	1752
Line amperes	0.87	0.95	1.06	1.21	1.4	1.61	1.34


ABB Motors and Mechanical Inc.

WINDING # 35WGG069

0.75 HP 3 PH 60 HZ 1765 RPM 460 V 3514M

Typical performance - not guaranteed values.

TORQUES (LB-FT) : PO=8 PU=4.4 LR=5.1 LRA=8.4



8/20/2026 ACPERF, record # 87322

