

ABB BALDOR RELIANCE III

Customer information packet

CCPX25226T

20HP, 3530//2930RPM, 3PH, 60HZ, 256TC, XPFC, F

Class - CLI GP C,D; CLII GP E,F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	256TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP E,F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 50 HZ 20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	380.0 V @ 50 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ 190.0 V @ 50 HZ
Agency Approvals	CSA EEV UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	48.000 A @ 208.0 V 44.000 A @ 230.0 V 40.000 A @ 190.0 V 22.000 A @ 460.0 V 20.000 A @ 380.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGZ651
Layout	09LY-000-321
Eff. date	06-26-2026
CD Diagram	CD0180
Poles	02
Leads	9#10
Proprietary	False
Created date	04-20-2019

Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	20.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0950M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.94 IN
Power Factor	91
Product Family	Chemical Process Features
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3530 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2033XPSLEV												
NO.							CC	010A				
S/N							TEMP CODE	T3C				
SPEC.	09-0000-1335						INV.TYPE	PWM				
CAT.NO.	CCPX25226T						C HP FR	60	C HP TO	90		
HP	20//15/20						CT HZ FROM	6	CT HZ TO	60		
VOLTS	230/460						VT HZ FROM	6	VT HZ TO	60		
AMPS	44/22//40/20						MAG CUR	5.8				
RPM	3530//2930						MX RPM	5400				
HZ	60//50/6	PH	3	CL	F	NOM.EFF.	91					
SER.F.	1.00	DES	A	SL HZ	1.2	WK2	1.28					
FRAME	256TC	RATING	40C AMB-CONT									
BLANK	55C AMB @ 1.0 SF, 60C RISE											
	1.15SF ON SINEWAVE						NEMA MG-1 PT.5,IP55					

AC Induction Motor Performance Data

Record # 54032

Typical performance - not guaranteed values

Winding: 09WGZ651-R011				Type: 0950M		Enclosure: XPFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		20		Full Load Torque		30 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		44/22		Breakdown Torque		167 LB-FT		
R.P.M.		3530		Pull-up Torque		33.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		51 LB-FT		
NEMA Design Code		A	KVA Code	H	Starting Current		160 A	
Service Factor (S.F.)		1		No-load Current		5.75 A		
NEMA Nom. Eff.		91	Power Factor	91	Line-line Res. @ 25°C		0.43337 Ω	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		58°C

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	65	83	89	91	91	91
Efficiency	89.4	92.7	92.9	92.4	91.4	90.1
Speed	3580.7	3566.7	3547.3	3526.6	3504.5	3479.4
Line amperes	8.04	12.2	17.1	22.4	28.2	34.2


ABB Motors and Mechanical Inc.

WINDING # 09WGZ651

Typical performance - not guaranteed values.

20 HP 3 PH 60 HZ 3530 RPM 460 V 0950M

TORQUES (LB-FT): PO=167 PU=33.7 LR=51 LRA=160



AC Induction Motor Performance Data

Record # 75709

Typical performance - not guaranteed values

Winding: 09WGZ651-R010				Type: 0950M		Enclosure: XPFC	
Nameplate Data				380 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		20//15		Full Load Torque		27.04 LB-FT	
Volts		230/460//190/380		Start Configuration		direct on line	
Full Load Amps		44/22//40/20		Breakdown Torque		161 LB-FT	
R.P.M.		3530//2930		Pull-up Torque		35.64 LB-FT	
Hz		60//50		Phase		3	
NEMA Design Code		A		KVA Code		H	
Service Factor (S.F.)		1		No-load Current		5.68 A	
NEMA Nom. Eff.		91		Power Factor		91	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps						Temp. Rise @ S.F. Load	
						Locked-rotor Power Factor	
						Rotor inertia	

Load Characteristics 380 V, 50 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	62	82	88	91	91	92
Efficiency	89.5	92.9	92.7	91.9	90.9	89.7
Speed	2983	2970	2952	2934	2914	2892
Line amperes	7.59	11.31	15.7	20.45	25.66	31.13


ABB Motors and Mechanical Inc.


WINDING # 09WGZ651

Typical performance - not guaranteed values.




15 HP 3 PH 50 HZ 2934 RPM 380 V 0950M

TORQUES (LB-FT): PO=161 PU=35.64 LR=53.94 LRA=156





CD0180


 LOW VOLTAGE
(2D)

 HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10:25:29 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1

CD0180