

ABB BALDOR RELIANCE III

Customer information packet

CCPX36466T

40HP, 1190RPM, 3PH, 60HZ, 364TC, A36062M, TEFC

Class - CLI GP C,D; CLII GP E,F,G

Division - Division I

Specifications

Enclosure	TEFC
Frame	364TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP E,F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV CSA UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	6-60
Current @ Voltage	49.000 A @ 460.0 V 98.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	49.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	-
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG1194
Layout	611742-778
Eff. date	10-20-2022
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	10-20-2022

KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36062M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.48 IN
Power Factor	80
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.00
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

NP3140L												
SPEC NO.	A36-8080-1194			CAT.NO.		CCPX36466T					FRAME	364TC
HP	40	VOLTS	230/460			PHASE	3	DESIGN	B	TYPE	P	
RPM	1190	AMPS	98/49			HZ	60	AMB	40	SF	1.00	
DRIVE END BEARING	65BC03J30X			DUTY	CONT	INSUL.CLASS			F			
OPP D.E. BEARING	65BC03J30X			ENCL	TEFC	CODE	G					
SF	1.15	WK2	20.223	MAG CUR	46/23			RPM MAX	1800			
CT HZ	6-60	VT HZ	6-60	CHP HZ	60-90			NEMA-NOM-EFF		94.1		
	SUITABLE @ 55C AMB @ 1.00SF						ON SINEWAVE IP66					
SER.NO.					MOTOR WEIGHT			908				

000613006PC		
CLASS I GROUP	C D X	NO.
CLASS II GROUP	E F G	
OPERATING TEMP CODE	T3C	

NP2496L	
MOBIL POLYREX EM	

000692000FX



AC induction motor performance data

Record #96080 - Typical performance - not guaranteed values

Winding	A36WG1194
Type	A3662M
Enclosure	TEFC

Nameplate data

Rated Output	40
Volts	230/460
Full Load Amps	98.8/49.4
R.P.M.	1190
Hz	60
Phase	3
KVA Code	G
Service Factor (S.F.)	1
NEMA Nom. Eff.	94.1
Power Factor	80
Duty	CONT
S.F. Amps	

480 V. 60 Hz:

High Voltage Connection


Full Load Torque	176 LB-FT
Start Configuration	direct on line
Breakdown Torque	561 LB-FT
Pull-up Torque	260 LB-FT
Locked-rotor Torque	330 LB-FT
Starting Current	341 A
No-load Current	22.48
Line-line Res. @ 25°C	0.158 Ω
Temp. Rise @ Rated Load	40°C
Temp. Rise @ S.F. Load	0°C
Locked-rotor Power Factor	25.4
Rotor inertia	20.1 lb-ft ²


Load Characteristics 480 V, 60 Hz, 40 HP

% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	5	41	62	72	78	81	82	0
Efficiency	0	87.5	92.2	93.7	94.1	93.5	92.9	0
Speed	1199	1197	1194	1192	1189	1186	1182	0
Line amperes	22.48	25.4	31.91	39.96	49.22	59.38	70.56	0

40 HP 3 PH 60 HZ 1190 RPM 480 V A3662M

TORQUES (LB-FT): PO=561.00 PU=260.00 LR=330.00 LRA=341.00





CONNECTION DIAGRAM
ACCESSORIES

MOTOR WINDING THERMOSTATS		
CONTACTS	_____ @ _____ ° C	
FIGURE NUMBER	_____	
CONTACT RATING		
VOLTS	CONTINUOUS AMPERES	INRUSH AMPERES
110-120	3. 0	30
220-240	1. 5	15
440-480	0. 75	7. 5
550-600	0. 60	6. 0

THERMOSTATS	
NORMALLY CLOSED	NORMALLY OPEN
FIGURE 1	FIGURE 4
FIGURE 2	FIGURE 5
FIGURE 3	FIGURE 6
FIGURE 7	FIGURE 8

CUSTOMER _____ CUSTOMER ORDER NO. _____ S.O. NO. _____

418174-006

418174-006

REV. DESC: LOADED TO BUS		
REV. LTR: A	VERSION: 01	TDR: 000000570390
FILE: \RAG\00013\849	REVISED: 10:16:21 12/07/2010	BY: RAGDRF
MTL: -		



BALDOR

A-C MOTOR CONNECTION ACCESSORIES

SH 1 of 1

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED



(N.P. 1575-B)

REV. DESC: FONT CHANGE FOR PDF SEARCHABLE		
REV. LTR: A	VERSION: 01	TDR: 000001009382
FILE: \MGA\00000\661	REVISED: 02:46:19 02/13/2020	BY: MGHMTT
MTL: —		

BALDOR - RELIANCE®

CONN DIAG — STANDARD 9 LEAD, DELTA-CONNECTED
SH 1 of 1

416820-002