ABB BALDOR RELIANCE

Customer information packet

CCPX36646T

60HP, 1780RPM, 3PH, 60HZ, 364TC, A3658M, TEFC
Class - CLI GP C,D; CLII GP E,F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/7/2026 9:50:22 AM

Specifications

Enclosure	TEFC
Frame	364TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP E,F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UL
	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	6-60
Current @ Voltage	140.000 A @ 230.0 V
	152.000 A @ 208.0 V
	70.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	70.0 a
Insulation Class	F

Part Detail

Revision	-
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4075
Layout	611742-778
Eff. date	07-28-2025
CD Diagram	CD0180
Poles	04
Leads	3#4,6#6
Proprietary	False
Created date	07-25-2025

Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A3658M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.48 IN
Power Factor	84
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.00
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

NP2496L
MOBIL POLYREX EM

000692000FX

000613006PC			
CLASS I GROUP	C D X	**NO.**	
CLASS II GROUP	E F G		
OPERATING TEMP CODE	T3C		

NP3140L												
SPEC NO.	A36-7817-4075			**CAT.NO.**	CCPX36646T					**FRAME**	364TC	
HP	60	**VOLTS**	230/460		**PHASE**	3	**DESIGN**	B	**TYPE**	P		
RPM	1780	**AMPS**	140/70		**HZ**	60	**AMB**	40	**SF**	1.00		
DRIVE END BEARING	65BC03J30X		**DUTY**	CONT		**INSUL.CLASS**	F					
OPP D.E. BEARING	65BC03J30X		**ENCL**	TEFC	**CODE**	G						
SF	1.15	**WK2**	13.42	**MAG CUR**	50/25		**RPM MAX**	2700				
CT HZ	6-60	**VT HZ**	6-60	**CHP HZ**	60-90		**NEMA-NOM-EFF**	95				
	SUIT FOR 55 DEG C AMB @ 1.0 SF				IP66							
SER.NO.				**MOTOR WEIGHT**	985							

DUTY MASTER ALTERNATING CURRENT MOTORS

611742-778

ENCLOSURE: TOTALLY ENCLOSED | SQUIRREL-CAGE INDUCTION | UNDERWRITER MOTOR

MOUNTING: FOOT, F-1 | E365TC/E364TC FRAME MOUNTING HOLES | COOLING: FAN COOLED EXPLOSION PROOF









DIMENSIONS ARE IN INCHES.
MOTOR WEIGHT (LBS)= 944±15% DEPENDING RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

FACE RUNOUT & ECCENTRICITY = .007 MAX. T.I.R.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

SHEET NUMBER 1 OF 1

611742-778

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 11:41:39 04/16/2019	TDR: 000001105246
MODEL NO. 611742-778			
BY: USJEDIL			C

BALDOR

E365/364TC FCXP F1 FOOT CI BOX/TACONITE SLINGERS/GROUND TAP

611742-778


CONNECTION DIAGRAM
ACCESSORIES
418174-006
MOTOR WINDING THERMOSTATS
CONTACTS _____ @ _____ °C
FIGURE NUMBER _____
CONTACT RATING
VOLTS
CONTINUOUS AMPERES
INRUSH AMPERES
110-120 3.0 30
220-240 1.5 15
440-480 0.75 7.5
550-600 0.60 6.0
THERMOSTATS
NORMALLY CLOSED
NORMALLY OPEN
FIGURE 1
FIGURE 2
FIGURE 3
FIGURE 4
FIGURE 5
FIGURE 6
FIGURE 7
FIGURE 8
P1
P2
CUSTOMER _____
CUSTOMER ORDER NO. _____
S.O. NO. _____
418174-006
REV. DESC: LOADED TO BUS
REV. LTR: A
VERSION: 01
TDR: 000000570390
FILE: \RAG\00013\849
REVISED: 10:16:21 12/07/2010
BY: RAGDRF
MTL: -
BALDOR
A-C MOTOR CONNECTION ACCESSORIES
SH 1 of 1

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1