

INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS – RPM III


ENCLOSURE: DRIP-PROOF FULLY-GUARDED
SPLASHPROOF, TOTALLY ENCLOSED

MOUNTING: FOOT, NEMA AC "C" FACE
METHOD OF DRIVE: COUPLED OR BELTED

COOLING: SELF-VENTILATED
NON-VENTILATED

ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

FRAMES C180ATCZ



- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
- (2) "U" AND "FU" VARY +.0000 - .0005
- (3) TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM.
FOR "X/P" TERMINAL BOX DIMENSIONS SEE 609989-1.
FOR MILL TYPE TERMINAL BOX DIMENSIONS SEE 609989-2.
- (4) "R" AND "FR" VARY +.000, -.015.
- (5) AA CONDUIT, TERMINAL BOX PROVIDED WITH DOUBLE KNOCKOUT.
- (6) AA PIPE TAP
- (7) OPPOSITE DRIVE END SHAFT SUPPLIED ONLY WHEN SPECIFIED.
- (8) "AK" VARIES +.000, -.003.
- (9) FACE RUNOUT AND ECCENTRICITY .004 MAX. T. I. R.
- (9) DRIVE END SHAFT DIMENSIONS PER 180T AC MOTOR SHAFT EXTENSION.
- (10) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF DPP, DRIVE END, ADD .25 TO "C" DIM. FOR BRACKET COVER.

TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7 OR C-1 MOUNTING IS SPECIFIED.
BOX LOCATED ON TOP WHEN SPECIFIED.

MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

FRAME	A	D(1)	E	G	H	J	D	P	T	BA	K	FK	BK	BB	BD	BF TAP	BF TAP "DEPTH"	AJ	AK(8)
C1811ATCZ-C1812ATCZ	9.00	4.50	3.75	.31	.44	1.50	8.88	8.75	1.88	2.75	4.38	4.38	.50	.25	8.75	1/2-13	.88	7.25	8.500

FRAME	C(10)	B	BS	2F	AH	N	N-W	UK(2)	V	R(4)	SQ.	LGTH	FN	FN-FW	FUK(2)	FV	FR(4)	SQ.	LGTH	WT. LBS.
C1811ATCZ	24.06	14.00	11.00	12.50	2.62	3.12	2.88	1.1250	2.62	.986	.250	1.75	2.44	2.25	1.1250	2.00	.986	.250	1.38	180
C1812ATCZ	25.56	15.50	12.50	14.00	2.62	3.12	2.88	1.1250	2.62	.986	.250	1.75	2.44	2.25	1.1250	2.00	.986	.250	1.38	215

STEEL TERMINAL BOX DIMENSIONS															
FRAME	MAX. AMPS	STANDARD SIZE						PART NUMBER	ONE SIZE LARGER						PART NUMBER
		AA(5)	AB	AC	AF	X	Y		AA(5)	AB	AC	AF	X	Y	
C180ATCZ	40	3/4 & 1"	7.31	5.75	1.94	4.38	5.00	705028-1-R	1-1/4 & 1-1/2	8.31	6.31	2.50	5.50	6.12	705029-1-R
	96	1-1/4 & 1-1/2	8.31	6.31	2.50	5.50	6.12	705029-1-R	2" & 2-1/2	9.44	6.69	3.19	7.00	7.62	705030-1-R

CAST IRON TERMINAL BOX DIMENSIONS															
FRAME	MAX AMPS	STANDARD SIZE						PART NUMBER	ONE SIZE LARGER						PART NUMBER
		AA(6)	AB	AC	AF	X	Y		AA(6)	AB	AC	AF	X	Y	
C180ATCZ	18	3/4	9.38	7.38	2.50	5.00	5.75	705028-2-S	1	9.38	7.38	2.50	5.00	5.75	705028-2-T
	40	1	9.38	7.38	2.50	5.00	5.75	705028-2-T	1-1/2	10.31	7.88	3.00	6.00	7.00	705029-2-R
	96	1-1/2	10.31	7.88	3.00	6.00	7.00	705029-2-R	2	10.31	7.88	3.00	6.00	7.00	705029-2-S

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: REVISE "D" DIMENSION TOLERANCE

REV. LTR: B

VERSION: 02

TDR: 000001150521

FILE: \RGG\00030\981

REVISED: 12:00:27 10/06/2020

BY: RGGNAS

MTL: -

BALDOR - RELIANCE®

DIMENSION DRAWING, C180ATCZ, TENV, DPP, FOOT MTG., NEMA AC C-FACE

SH 1 of 1