


INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS - RPM III

ENCLOSURE: DRIP-PROOF FULLY-GUARDED MOUNTING: FOOT, "C" FACE COOLING: SELF-VENTILATED ACCESSORIES: PROVISIONS FOR
 SPLASHPROOF, TOTALLY ENCLOSED METHOD OF DRIVE: COUPLED OR BELTED NON-VENTILATED TACHOMETER MOUNTING
 ONLY WHEN SPECIFIED

DC180ATY-DC180ATCZ



DIMENSIONS ARE IN INCHES

FRAME	FLANGE	A	DC(1)	E	G	H	J	K	FK	BK	D	P	T	BA	BB(7)	BD	BF TAP	BF TAP	AJ	AK(4)	A.C. SHAFT
DC189ATY	ND. 2	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	5.88	4.500	140TC EXT.
DC189ATCZ	ND. 1	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.25	8.75	1/2-13	.88	7.25	8.500	180TC EXT.
DC1810ATY	ND. 2	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	5.88	4.500	140TC EXT.
DC1810ATCZ	ND. 1	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.25	8.75	1/2-13	.88	7.25	8.500	180TC EXT.
DC1811ATY	ND. 2	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	5.88	4.500	140TC EXT.
DC1811ATCZ	ND. 1	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.25	8.75	1/2-13	.88	7.25	8.500	180TC EXT.

FRAME	FLANGE	C(5)	B	2F	N	N-W	UK(2)	V	AH	R(3)	SQ	LGTH	AA	AB	AC	AF	X	Y	YZ	WT.
DC189ATY	ND. 2	18.81	11.62	10.00	2.44	2.25	.8750	2.00	2.12	.771	.188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	130
DC189ATCZ	ND. 1	19.44	11.62	10.00	3.06	2.88	1.1250	2.62	2.62	.986	.250	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	130
DC1810ATY	ND. 2	19.56	12.38	11.00	2.44	2.25	.8750	2.00	2.12	.771	.188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	155
DC1810ATCZ	ND. 1	20.19	12.38	11.00	3.06	2.88	1.1250	2.62	2.62	.986	.250	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	155
DC1811ATY	ND. 2	21.06	13.88	12.50	2.44	2.25	.8750	2.00	2.12	.771	.188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	185
DC1811ATCZ	ND. 1	21.69	13.88	12.50	3.06	2.88	1.1250	2.62	2.62	.986	.250	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	185

- (1) *D* DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES. TOLERANCE +.00/- .06.
 (2) *U* VARIES +.0000, -.0005.
 (3) *R* VARIES +.000, -.015.
 (4) *AK* VARIES +.000, -.003.
 FACE RUNDUT AND ECCENTRICITY .004 MAX. T. I. R.

- (5) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF DPP, DRIVE END, ADD .25 TO *C* DIM. FOR BRACKET COVER.
 (6) TERMINAL BOX CAN BE ROTATED TO REPOSITION CONDUIT CONNECTION.
 IF MOUNTING CLEARANCE DETAILS ARE REQUIRED CONSULT FACTORY.
 (7) *BB* OF .25 IS A MINIMUM VALUE.

MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: REVISE "D" DIM TOLERANCE	VERSION: 04	TDR: 000001148815
REV. LTR: D	FILE: \RGG\00030\373	REVISD: 03:18:10 09/15/2020
MTL: -	BY: RGGNAS	

BALDOR - RELIANCE®

DIMENSION DRAWING, DC180ATY - DC180ATCZ, DPP, TENV, FOOT MTG.

SH 1 of 1