

ABB BALDOR RELIANCE III

Customer information packet

CD2015P-2

15HP, 1750/2300RPM, DC, 258ATC, DPFG, F1

Specifications


Armature Voltage	240 V
Base Speed	1750 rpm
Enclosure	DPFG
Field Voltage	120 V
	240 V
Output Power	15.000 HP
Agency Approvals	CSA
Ambient Temperature	40 °C
Armature Current	55.0 a
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Field Winding Type	STR. SHUNT
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	29.84 IN
Service Factor	1.00
Shaft Diameter	1.624 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger
Thermal Device - Bearing	None

Part Detail

Revision	A
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	K0035B A
Layout	880-1
Eff. date	02-26-2020
CD Diagram	15209
Poles	00
Leads	
Proprietary	False
Created date	12-12-2019

Nameplate

NP1734										
CAT.NO.				MODEL	T25S8006					
HP	15	RPM	1750/2300		FRAME		0258ATC			
ARM V	240		ARM A		55.00	WOUND		STR. SHUNT		
FLD V	120/240		FLD A		2.52-1.62/1.26-.81					
CONN			OHMS				CL	F		
ENCL	DPFG		DUTY		CONT		MX AMB		40	
P CODE	D		CTSR				SER.F.		1.0	
S/N				E/S	K0035B A					
	-									
O.D.E. BRG.	6207	D.E. BRG.		6209	BRUSH		150986-25-1		QTY	4




CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC:	REV. "D" DIM TO +.000 -.060 ONLY		
REV. LTR:	B	VERSION: 01	TDR: 000000752566
FILE:	\\RGG\00019\509	REVISED: 10:47:40 06/20/2012	BY: RGGNAS
MTL:	-		

BALDOR

DIM SHEET
SH 1 of 1

15209



NOTE:
MATERIAL .005 MINIMUM FULL HARD ALUMINUM DULL FINISH.
TEMP. RANGE -20°C TO +125°C MAXIMUM.
FOR INDOOR AND OUTDOOR MOUNTING BACK.
METAL, PRESSURE SENSITIVE BACK. MUST MEET CSA STANDARD.
THE CSA IDENTIFYING MARK OF THE LABEL MANUFACTURER MUST APPEAR IN THE UPPER RIGHT HAND CORNER AS INDICATED.

MATL: NOTED			
REV:	G	CHANGE ALL "NAMEPLATE" TEXT TO "LABEL"	
60Z91		SCALE: —	BY: BKW
		FILE: CHB00002485	REVISED: 02/19/97
		TDR: 0115147	

BALDOR ELECTRIC Co.

LABEL, CONNECTIONS AND TERMINAL MARKINGS DC

15209