


INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS - RPM III

ENCLOSURE:DRIP-PROOF FULLY-GUARDED
SPLASHPROOF, TOTALLY ENCLOSED
MOUNTING:FOOT,"C" FACE
METHOD OF DRIVE:COUPLED OR BELTED

COOLING:SELF-VENTILATED
NON-VENTILATED
ACCESSORIES:PROVISIONS FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

DC2112ATCZ



- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .03 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
- (2) "U" VARIES +.0000, -.0005.
- (3) "R" VARIES +.000, -.015.
- (4) "AK" VARIES +.000, -.003.
FACE ROUNDT AND ECCENTRICITY .004 MAX. T. I. R.
- (5) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF OPP. DRIVE END, ADD .25 TO "C" DIM. FOR BRACKET COVER.
- (6) TERMINAL BOX CAN BE ROTATED TO REPOSITION CONDUIT CONNECTION.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED CONSULT FACTORY.

MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.

DIMENSIONS ARE IN INCHES

FRAME	A	D(1)	E	G	H	J	K	FK	BK	D	P	T	BA	BB	BD	BF TAP	BF TAP DEPTH*	AJ	AK(4)
DC2112ATCZ	10.31	5.25	4.25	.38	.44	1.62	4.44	3.56	.62	10.44	10.31	1.88	3.50	.25	8.75	1/2-13	.88	7.25	8.500

FRAME	C(S)	B	2F	DRIVE END SHAFT AND KEY							A. C. SHAFT EXT. REBT.	TERMINAL BOX DIMENSIONS							WT. LBS.	
				N	N-W	UK(2)	V	AH	R(3)	SQ.		LGTH	AA	AB	AC	AF	X	Y		YZ
DC212ATCZ	27.22	17.25	16.00	3.06	2.88	1.1250	2.62	4.82	986	250	1.81	180T	3/4	6.88	5.56	1.69	3.38	3.88	3.25	3.93

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: CHANGE LAB OFFICE TO 015 FROM 018		
REV. LTR: A	VERSION: 01	TDR: 000000872511
FILE: \RSN\00029\755	REVISED: 01:05:56 09/22/2014	BY: RSNDLB2
MTL: -		

BALDOR

DIMENSION SHEET DC2112ATCZ

SH 1 of 1