ABB BALDOR RELIANCE

Customer information packet

CD5318

1HP, 1750RPM, DC, 56C, 3535D, TEFC, F1
Class - None
Division -

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 12:10:06 AM

Specifications

Armature Voltage	180 V
Base Speed	1750 rpm
Enclosure	TEFC
Field Voltage	100 V
	200 V
Frame	56C
Frame Material	Steel
Haz Area Class and Group	None
Output Power	1.000 HP
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Armature Current	5.0 a
Armature Inertia	13.657 lb-ft2
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Field Winding Type	SHUNT
Heater Indicator	No Heater
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Lead Hole
Motor Lead Quantity/Wire Size	2 @ 14 AWG
	4 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	16.29 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00

Part Detail

Revision	R
Type	DC
Mech. spec.	35P442
Base	
Status	PRD/A
Elec. spec.	35WGZ391
Layout	35LYP442
Eff. date	10-28-2024
CD Diagram	CD0860C01
Poles	00
Leads	
Proprietary	False
Created date	01-01-0001

Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP0111L					
CAT.NO.	CD5318				
SPEC.	35P442Z391				
HP	1	**ENCL**	TEFC		
RPM	1750				
FRAME	56C	**TYPE**	3535D		
ARM V	180	**ARM A**	5		
FLD V	200/100	**FLD A**	.3/.6		
INSUL	F	**AMB.**	40		
DUTY	CONT	**SUPPLY**	1.3		
BRG/DE	6205	**BRG/ODE**	6203		
BRUSHES	2/BP5000T07				
		BLANK			
SER.					
BLANK					
APRV-CSA		**APRV-UL**			

Accessories

Part number	Description	Multiplier
TK3500	TACHO MOUTING KIT TK3500	A8

DC Motor Performance Data
Record # 279
Typical performance - not guaranteed values

Winding: 35WGZ391-R001	**Type:** 3535D	**Enclosure:** TEFC

Nameplate Data	
Rated Output (HP)	1
R.P.M.	1750
Armature Volts	180
Armature Amps	5
Field Volts	200 / 100
Field Amps	0.3 / 0.6
Rating - Duty	40C AMB-CONT
Form Factor	1.3

General Characteristics	
Armature Resistance @ 25ºC	1.898 Ω
Commutating Winding Resistance @ 25ºC	1.363 Ω
Shunt Winding Resistance @ 25ºC	686.4 Ω
Temp. Rise @ Rated Load	102°C

Load Characteristics at 180 Armature Volts, 200 Field Volts, 0.27 Field Amps

Load Point	**1**	**2**	**3**	**4**	**5**	**6**	**7**
Armature Amps	0.35	1.4	2.5	3.7	4.9	6.4	7.9
R.P.M.	1945	1878	1831	1795	1760	1739	1714
Torque (LB-FT)	0	0.75	1.5	2.25	3	3.75	4.5


ABB Motors and Mechanical Inc.


WINDING # 35WGZ391

Typical performance - not guaranteed values.

1 HP DC 1750 RPM 180 V ARM 200/100 V FLD 3535D


ENCL: TEFC DUTY: CONT CL: F




35LYP442
510-516 = 13.82
520-524 = 14.82
528-535 = 16.20
3.60
.79 (REF)
2.06
1.88
BOTTOM OF NAMEPLATE
.19 KEY
1.38 LONG
(ENDMILLED KEYWAY)
Ø7.19
Ø6.49
Ø4.500
4.497
Ø.6250
.6245
BRUSH LOCATION
2 PLACES 180° APART
4 SLOTS
.34 WIDE
.75
3.00
2.75
4.50
Ø6.61
LEAD HOLE
Ø.88
45°
45°
7.76
3.38
3.50
3.44
4 HOLES
.38-16 TAP
ON Ø5.88 B.C
2.44
2.44
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOADING OF SWD DWG FOR 2D TO 3D CONVERSION - PKG16
REV: F
VERSION: 04
REVISED: 11:11:35 02/04/2019
TDR: 000001098202
MODEL NO. 35LYP442
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
STD HORZ "C" 35DC NEMA 56C TEFC 2P W/BOLT ON BASE MFTK
SH 1 of 1
35LYP442

CD0860C01

SHUNT WOUND



CONNECTION	DIRECTION OF ROTATION			
	CWDE		CCWDE	
	POS TERM (+)	NEG TERM (−)	POS TERM (+)	NEG TERM (−)
HIGH VOLTAGE	A1 F1 CONNECT F2 & F3	A2 F4	A2 F1 CONNECT F2 & F3	A1 F4
LOW VOLTAGE	A1 F1 & F3	A2 F2 & F4	A2 F1 & F3	A1 F2 & F4

NOTES:

1. LIMIT STARTING INRUSH CURRENT TO NOT MORE THAN 3 TIMES RATED AMPERES BY ENERGIZING THE FULL SHUNT FIELD BEFORE BRINGING THE ARMATURE VOLTAGE UP SLOWLY OR IN STEPS.
2. OPTIONAL FIELD REOSTAT MAY BE CONNECTED IN SERIES WITH THE SHUNT FIELD.
3. OPTIONAL THERMOSTAT LEADS ARE MARKED J,J.

CD0860C01

REV. DESC: NEW, REPLACE CD0860			BALDOR ELECTRIC Co.
REV. LTR: –	BY: JLP	REVISED: 15:35:22 11/03/2004	TDR: 347796
CD0860C01		FILE: AAA00121477	REF: CD0860C01
		MTL: –	DC CONNECTION DIAGRAM, SHUNT FIELD, 6 LEAD, DUAL VOLTAGE