Customer information packet

CDM3537

.5HP, 3450RPM, 3PH, 60HZ, 56C, 3414M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 1:29:49 PM

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CCSA US
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	1.700 A @ 208.0 V
	1.800 A @ 230.0 V
	.900 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	M
Type	AC
Mech. spec.	34M848
Base	
Status	PRD/A
Elec. spec.	34WGR421
Layout	34LYM848
Eff. date	12-01-2025
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	07-27-2016

Heater Indicator	No Heater
High Voltage Full Load Amps	0.9 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	P
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3414M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.35 IN
Power Factor	75
Product Family	Dirty Duty Plus
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3659							
CAT.NO.	CDM3537						
SPEC.	34M848R421G1				**ENCL**	TEFC	
FRAME	56C		**H.P.**	.5			
VOLTS	230/460						
AMPS	1.8/.9				**IP**	56	
R.P.M.	3450						
HZ.	60	**PH.**	3	**CLASS**	F		
SER.F.	1.25	**DES.**	B	**CC**			
NEMA NOM. EFF.	68						
RATING	40C AMB-CONT						
DE	6203	**ODE**	6203				
GREASE	POLYREX EM						
SN							
	50C AT 1.0 SF						
	SFA 2/1						

AC Induction Motor Performance Data
Record # 58290
Typical performance - not guaranteed values

Winding: 34WGR421-R001	**Type:** 3414M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.5	**Full Load Torque**	0.763 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			1.8/.9	**Breakdown Torque**	4.6 LB-FT
R.P.M.			3450	**Pull-up Torque**	3.07 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	3.86 LB-FT
NEMA Design Code	B	**KVA Code**	P	**Starting Current**	8.39 A
Service Factor (S.F.)			1.25	**No-load Current**	0.626 A
NEMA Nom. Eff.	68	**Power Factor**	75	**Line-line Res. @ 25ºC**	26.14 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	51°C
S.F. Amps			2/1	**Temp. Rise @ S.F. Load**	59°C
				Locked-rotor Power Factor	69.4

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	45	58	67	75	80	84	80
Efficiency	39.7	56.1	64.1	69.1	70.6	72.3	70.6
Speed	3536.7	3517.5	3497.4	3469	3451.9	3427.2	3452
Line amperes	0.674	0.731	0.817	0.915	1.04	1.15	1.04


ABB Motors and Mechanical Inc.

WINDING # 34WGR421

0.5 HP 3 PH 60 HZ 3450 RPM 460 V 3414M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=4.6 PU=3.07 LR=3.86 LRA=8.39



11/16/2026 ACPERF, record # 58290


AC Induction Motor Performance Data
Record # 73819
Typical performance - not guaranteed values

Winding: 34WGR421-R001	**Type:** 3414M	**Enclosure:** TEFC


Nameplate Data				**230 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			.5	**Full Load Torque**	0.763 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			1.8/.9	**Breakdown Torque**	4.6 LB-FT
R.P.M.			3450	**Pull-up Torque**	3.07 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	3.86 LB-FT
NEMA Design Code	B	**KVA Code**	P	**Starting Current**	16.78 A
Service Factor (S.F.)			1.25	**No-load Current**	1.25 A
NEMA Nom. Eff.	68	**Power Factor**	75	**Line-line Res. @ 25ºC**	6.46 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	51°C
S.F. Amps			2/1	**Temp. Rise @ S.F. Load**	57°C
				Locked-rotor Power Factor	69.4
				Rotor inertia	0.013 LB-FT2


Load Characteristics 230 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	45	58	68	75	80	84	80
Efficiency	39.6	56.2	64.1	69.1	70.6	71.9	70.6
Speed	3537	3518	3497	3469	3452	3427	3452
Line amperes	1.35	1.46	1.63	1.83	2.08	2.3	2.08


ABB Motors and Mechanical Inc.
WINDING # 34WGR421
0.5 HP 3 PH 60 HZ 3450 RPM 230 V 3414M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=4.6 PU=3.07 LR=3.86 LRA=16.78
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (0.5 HP)
11/16/2026 ACPERF, record # 73819

34LYM848





FRONT END DETAIL

PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: LOAD TO SOLIDWORKS - REV "-"			
REV: A	VERSION: 01	REVISED: 02:01:55 04/17/2023	TDR: 000001201165
34LYM848	MODEL NO. 34LYM848		REF: -
	BY: ENFRAJ0		


BALDOR - RELIANCE®

HOR 56C TEFC 34M DDP (S/P032-002-002) LOW RES ENDRINGS

34LYM848

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS