

ABB BALDOR RELIANCE III

Customer information packet

CDP3440-V24

.75HP, 1800RPM, DC, 56C, 3424P, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Armature Voltage	24 V
Base Speed	1800 rpm
Enclosure	TEFC
Frame	56C
Frame Material	Steel
Haz Area Class and Group	None
Output Power	0.750 HP
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Armature Current	29.4 a
Armature Inertia	8.264 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Haz Area Division	Not Applicable
Heater Indicator	No Heater
Insulation Class	H
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	14.51 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End

Part Detail

Revision	M
Type	DC
Mech. spec.	34-6893
Base	
Status	PRD/A
Elec. spec.	34WGZ611
Layout	34LY6893
Eff. date	10-25-2024
CD Diagram	CD0194
Poles	00
Leads	
Proprietary	False
Created date	01-01-0001

Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP0111L			
CAT.NO.	CDP3440-V24		
SPEC.	34-6893Z611		
HP	.75	ENCL	TEFC
RPM	1800		
FRAME	56C	TYPE	3424P
ARM V	24	ARM A	29.4
FLD V		FLD A	
INSUL	H	AMB.	40
DUTY	CONT	SUPPLY	A
BRG/DE	6203	BRG/ODE	6203
BRUSHES	2/BP5104BV01		
	BLANK		
SER.			
BLANK	---		
APRV-CSA		APRV-UL	


ABB Motors and Mechanical Inc.

WINDING # 34WGZ611


0.75 HP DC 1800 RPM 24 V 3424P

Typical performance - not guaranteed values.


ENCL: TEFC DUTY: CONT CL: H



7/8/2026, DCPERF, VER 2.0.06, record 499



CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -			
REV: E	ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."		
CD0194	SCALE: -	BY: CK	REVISED: 07/28/95
	FILE: AAA00004503	TDR: 0078737	

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194