ABB BALDOR RELIANCE

Customer information packet

CDRX18344T-5

3HP, 1755RPM, 3PH, 60HZ, 182TC, XPFC, F1
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 3:12:09 PM

Specifications

Enclosure	XPFC
Frame	182TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	3.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.3 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	06WGX319
Layout	06LYH515
Eff. date	08-04-2022
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	07-19-2019

IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0632M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.31 IN
Power Factor	77
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	06-0000-0182			**INV.TYPE**	PWM						
CAT.NO.	CDRX18344T-5			**C HP FR**	60	**C HP TO**	90				
HP	3			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	575			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	3.3		**MAG CUR**	1.7							
RPM	1755		**MX RPM**	2700							
HZ	60	**PH**	3	**CL**	F	**NOM.EFF.**	89.5				
SER.F.	1.00	**DES**	B	**SL HZ**	1.5	**WK2**	0.3				
FRAME	182TC	**RATING**	40C AMB-CONT								
	1.15 SF SINEWAVE										
	55C AMB @ 1.0SF			NEMA MG-1 PT 5,IP55							

AC Induction Motor Performance Data
Record # 77531
Typical performance - not guaranteed values

Winding: 06WGX319-R028	**Type:** 0632M	**Enclosure:** XPFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			3	**Full Load Torque**	9.05 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			3.3	**Breakdown Torque**	33 LB-FT
R.P.M.			1755	**Pull-up Torque**	18.2 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	20.3 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	23.8 A
Service Factor (S.F.)			1	**No-load Current**	1.7 A
NEMA Nom. Eff.	89.5	**Power Factor**	77	**Line-line Res. @ 25ºC**	6.2 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	35°C
				Locked-rotor Power Factor	41.5
				Rotor inertia	0.298 LB-FT2

Load Characteristics 575 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	38	59	71	77	81	83
Efficiency	83	88.4	89.7	89.6	89	87.6
Speed	1790	1779	1769	1757	1744	1730
Line amperes	1.86	2.22	2.71	3.27	3.92	4.69


ABB Motors and Mechanical Inc.


WINDING # 06WGX319

3 HP 3 PH 60 HZ 1755 RPM 575 V 0632M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=33 PU=18.2 LR=20.3 LRA=23.8





06LYH515
(614-643) =18.37
8.62
2.75
2.62
.25
.25 KEY
1.75 LONG
Ø10.12
Ø8.500
8.497
HAZARDOUS
LOCATIONS
Ø8.960 +.00 -.02
1.1250
1.1245
SLINGER
6 HOLES
.41 DIA.
4.50
3.49
5.50
.50
8.00
DRAIN FITTING
(EA. END)
13.70
5.03
5.06
2.04
45°
45°
9.43
4.50 +.00 -.06
4 HOLES
.50-13 TAP
Ø7.25 B.C.
LEAD HOLE
.75-14 N.P.T.
3.75
3.75
6.53
4.38
8.76
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: A
VERSION: 01
REVISED: 02:03:32 01/26/2023
TDR: 000001201906
MODEL NO. 06LYH515
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ 182-4TC XPFC M CL I-GP C&D, DRILL RIG
06LYH515


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1