

ABB BALDOR RELIANCE III

Customer information packet

CDPWD3310

.25HP, 1750RPM, DC, 56C, 3320P, TENV, F1

Specifications

Armature Voltage	90 V
Base Speed	1750 rpm
Enclosure	TENV
Frame	56C
Frame Material	Steel
Output Power	0.250 HP
Agency Approvals	CE
	CSA
	UR
Ambient Temperature	40 °C
Armature Current	2.5 a
Armature Inertia	7.804 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 18 AWG, A
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	12.25 IN
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible

Part Detail


Revision	AM
Type	DC
Mech. spec.	33-2142
Base	
Status	PRD/A
Elec. spec.	33WGZ118
Layout	33LY2142
Eff. date	08-20-2024
CD Diagram	CD0194
Poles	00
Leads	2#18 A CD0194 Y
Proprietary	False
Created date	01-01-0001

Shaft Slinger Indicator


Shaft Slinger

Nameplate

NP1509					
CAT.NO.	CDPWD3310				
SPEC.	33-2142Z118				
HP	.25	ENCL		TENV	
RPM	1750 1/MIN				
FRAME	56C	TYPE		3320P	
ARM V	90	ARM A		2.5	
FLD V		FLD A			
INSUL	F	AMB.		40	
DUTY	S1 CONT	SUPPLY		1.3	
BRG/DE	6203	BRG/ODE		6203	
BRUSHES	2/BP5011T01				
	IP55	BLANK			
SER.					
BLANK	KW.18 KG10 IC410				
APRV-CSA	Y	APRV-UL	Y	APRV-CE	Y



CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -

REV: E

ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."

CD0194

SCALE: -

BY: CK

REVISED: 07/28/95

FILE: AAA00004503

TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194