

ABB BALDOR RELIANCE III

Customer information packet

CDPWD3326

.5HP, 1750RPM, DC, 56C, 3336P, TENV, F1

Specifications

Armature Voltage	180 V
Base Speed	1750 rpm
Enclosure	TENV
Frame	56C
Frame Material	Steel
Output Power	0.500 HP
Agency Approvals	CE
	CSA
	UR
Ambient Temperature	40 °C
Armature Current	2.5 a
Armature Inertia	8.424 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 18 AWG, A
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	14.94 IN
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible

Part Detail

Revision	AU
Type	DC
Mech. spec.	33-2154
Base	
Status	PRD/A
Elec. spec.	33WGZ139
Layout	33LY2154
Eff. date	08-20-2024
CD Diagram	CD0194
Poles	00
Leads	2#18 A 4.5" OUT MTR Y
Proprietary	False
Created date	01-01-0001

Shaft Slinger Indicator

Shaft Slinger

Nameplate

NP1509					
CAT.NO.	CDPWD3326				
SPEC.	33-2154Z139				
HP	.5	ENCL		TENV	
RPM	1750 1/MIN IC410				
FRAME	56C	TYPE		3336P	
ARM V	180	ARM A		2.5	
FLD V		FLD A			
INSUL	F	AMB.		40	
DUTY	CONT	SUPPLY			1.3
BRG/DE	6203	BRG/ODE			6203
BRUSHES	2/BP5011CV01				
	IP55	BLANK			
SER.					
BLANK	KW.37 KG14				
APRV-CSA	Y	APRV-UL	Y	APRV-CE	Y

DC Motor Performance Data

Record # 2018

Typical performance - not guaranteed values

Winding: 33WGZ139-R010		Type: 3336P		Enclosure: TENV	
Nameplate Data		General Characteristics			
Rated Output (HP)	0.5	Armature Resistance @ 25°C		3.08 Ω	
R.P.M.	1750				
Armature Volts	180	Voltage Constant		95.88 v/krpm	
Armature Amps	2.5				
Field Volts		Armature Inductance		28.39697 mH	
Field Amps		Armature Inertia		8.4241 LI ²	
Rating - Duty	40C AMB-CONT				
Form Factor	1.3				

Load Characteristics at 180 Armature Volts

Load Point	1	2	3	4	5	6	7
Armature Amps	0.15	0.65	1.2	1.7	2.2	2.7	3.2
R.P.M.	1880	1848	1831	1803	1781	1762	1745
Torque (LB-FT)	0	0.365	0.752	1.117	1.504	1.869	2.234


ABB Motors and Mechanical Inc.


WINDING # 33WGZ139

Typical performance - not guaranteed values.


0.5 HP DC 1750 RPM 180 V 3336P

ENCL: TENV DUTY: CONT CL: F





CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -			
REV:	E	ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."	
CD0194		SCALE: -	BY: CK
		FILE: AAA00004503	TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194