

ABB BALDOR RELIANCE III

Customer information packet

CDRX21364T

3HP, 1165//970RPM, 3PH, 60/50HZ, 213TC, XPFC,
Class - CLI GP C,D
Division - Division I

Specifications

Enclosure	XPFC
Frame	213TC
Frame Material	Iron
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ 2.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 190.0 V @ 50 HZ 230.0 V @ 60 HZ 380.0 V @ 50 HZ
Agency Approvals	UL CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	3.800 A @ 380.0 V 4.500 A @ 460.0 V 7.600 A @ 190.0 V 9.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	07WGX970
Layout	07LYJ232
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	06-21-2019

Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.8 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	20.78 IN
Power Factor	72
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV												
NO.							CC	010A				
S/N							TEMP CODE	T3C				
SPEC.	07-0000-0151						INV.TYPE	PWM				
CAT.NO.	CDRX21364T						C HP FR	60	C HP TO	90		
HP	3//2						CT HZ FROM	6	CT HZ TO	60		
VOLTS	230/460//190/380						VT HZ FROM	6	VT HZ TO	60		
AMPS	9/4.5//7.6/3.8				MAG CUR		4.8/2.4					
RPM	1165//970				MX RPM		2700					
HZ	60//50	PH	3	CL	F	NOM.EFF.	89.5					
SER.F.	1.00	DES	B	SL HZ	1.8	WK2	0.895					
FRAME	213TC	RATING		40C AMB-CONT								
	55C AMB @ 1.0 SF											
	1.15 SF SINEWAVE						NEMA MG-1 PT 5,IP55					

AC Induction Motor Performance Data

Record # 74893

Typical performance - not guaranteed values

Winding: 07WGX970-R005			Type: 0736M		Enclosure: TEFC		
Nameplate Data			380 V, 50 Hz: High Voltage Connection				
Rated Output (HP)		3	Full Load Torque		10.88 LB-FT		
Volts		230/460//190/380	Start Configuration		direct on line		
Full Load Amps		9/4.5//7.6/3.8	Breakdown Torque		49.79 LB-FT		
R.P.M.		1165//970	Pull-up Torque		28.43 LB-FT		
Hz		60//50	Phase		3	Locked-rotor Torque	34.29 LB-FT
NEMA Design Code		B	KVA Code		K	Starting Current	31.53 A
Service Factor (S.F.)					1	No-load Current	2.23 A
NEMA Nom. Eff.		89.6	Power Factor		72	Line-line Res. @ 25°C	3 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		27°C	
S.F. Amps				Temp. Rise @ S.F. Load		32°C	
				Locked-rotor Power Factor		26.9	
				Rotor inertia		0.895 LB-FT2	

Load Characteristics 380 V, 50 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	30	48	60	67	72	75
Efficiency	79	86.1	88.2	88.5	88.3	86.9
Speed	993	987	980	972	965	955
Line amperes	2.4	2.75	3.24	3.82	4.46	5.22


ABB Motors and Mechanical Inc.

WINDING # 07WGX970

Typical performance - not guaranteed values.

2 HP 3 PH 50 HZ 972 RPM 380 V 0736M

TORQUES (LB-FT) : PO=49.79 PU=28.43 LR=34.29 LRA=31.53



AC Induction Motor Performance Data

Record # 74894

Typical performance - not guaranteed values

Winding: 07WGX970-R005			Type: 0736M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		3//2		Full Load Torque		13.61 LB-FT
Volts		230/460//190/380		Start Configuration		direct on line
Full Load Amps		9/4.5//7.6/3.8		Breakdown Torque		51.71 LB-FT
R.P.M.		1165//970		Pull-up Torque		25.77 LB-FT
Hz	60//50	Phase	3	Locked-rotor Torque		31.08 LB-FT
NEMA Design Code		B	KVA Code	Starting Current		32.19 A
Service Factor (S.F.)		1		No-load Current		2.26 A
NEMA Nom. Eff.		89.6	Power Factor	Line-line Res. @ 25°C		3 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		34°C
S.F. Amps				Temp. Rise @ S.F. Load		41°C
				Locked-rotor Power Factor		23.3
				Rotor inertia		0.895 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	35	54	65	72	75	76
Efficiency	82.8	88.3	89.6	89.6	88.9	87.3
Speed	1192	1184	1176	1166	1156	1143
Line amperes	2.48	2.96	3.62	4.41	5.29	6.33

ABB Motors and Mechanical Inc.

WINDING # 07WGX970

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 1166 RPM 460 V 0736M

TORQUES (LB-FT) : PO=51.71 PU=25.77 LR=31.08 LRA=32.19

