

ABB BALDOR RELIANCE III

Customer information packet

CDRX25244T-5

20HP, 1770RPM, 3PH, 60HZ, 256TC, XPFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	256TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	19.200 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	19.2 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	J
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGT507
Layout	09LY-000-582
Eff. date	02-14-2024
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	06-25-2019

IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0960M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	26.00 IN
Power Factor	83
Product Family	Hazardous Location Motor
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV														
NO.						CC	010A							
S/N						TEMP CODE			T3C					
SPEC.	09-0000-1447					INV.TYPE			PWM					
CAT.NO.	CDRX25244T-5					C HP FR		60		C HP TO		90		
HP	20					CT HZ FROM			6		CT HZ TO		60	
VOLTS	575					VT HZ FROM			6		VT HZ TO		60	
AMPS	19.2					MAG CUR								
RPM	1770					MX RPM			2700					
HZ	60	PH	3	CL	F	NOM.EFF.		93						
SER.F.	1.00	DES		A	SL HZ	1	WK2		2.62					
FRAME	256TC		RATING		40C AMB-CONT									
	55C AMB @ 1.0 SF, 60C RISE													
	1.15SF ON SINEWAVE					NEMA MG-1 PT.5,IP55								

AC Induction Motor Performance Data

Record # 76570

Typical performance - not guaranteed values

Winding: 09WGT507-R013			Type: 0960M		Enclosure: XPFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		20	Full Load Torque		59.29 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		19.2	Breakdown Torque		231 LB-FT		
R.P.M.		1770	Pull-up Torque		126 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque		140 LB-FT		
NEMA Design Code		A	KVA Code		J	Starting Current	158 A
Service Factor (S.F.)		1	No-load Current		8.28 A		
NEMA Nom. Eff.		93	Power Factor		83	Line-line Res. @ 25°C	0.524 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		58°C
S.F. Amps					Temp. Rise @ S.F. Load		69°C
					Locked-rotor Power Factor		26.9
					Rotor inertia		2.65 LB-FT2

Load Characteristics 575 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	45	67	78	83	86	87
Efficiency	89.2	93	93.7	93.6	93.1	92.4
Speed	1793	1786	1779	1772	1764	1755
Line amperes	9.41	11.99	15.34	19.19	23.44	27.92


ABB Motors and Mechanical Inc.


WINDING # 09WGT507

Typical performance - not guaranteed values.




20 HP 3 PH 60 HZ 1770 RPM 575 V 0960M

TORQUES (LB-FT): PO=231 PU=126 LR=140 LRA=158





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1