

ABB BALDOR RELIANCE III

Customer information packet

CDRX141524T

1.5HP, 3500//2900RPM, 3PH, 60/50HZ, 143TC, XP

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	143TC
Frame Material	Steel
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ 1.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 190.0 V @ 50 HZ 230.0 V @ 60 HZ 380.0 V @ 50 HZ
Agency Approvals	UL CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	1.700 A @ 380.0 V 1.900 A @ 460.0 V 3.400 A @ 190.0 V 3.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	-
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WGM760
Layout	35LYX732
Eff. date	06-19-2019
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	06-13-2019

Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.34 IN
Power Factor	85
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV												
NO.							CC	010A				
S/N							TEMP CODE	T3C				
SPEC.	35-0000-0186						INV.TYPE	PWM				
CAT.NO.	CDRX141524T						C HP FR	60	C HP TO	90		
HP	1.5//1						CT HZ FROM	6	CT HZ TO	60		
VOLTS	230/460//190/380						VT HZ FROM	6	VT HZ TO	60		
AMPS	3.8/1.9//3.4/1.7				MAG CUR		1.8/9					
RPM	3500//2900				MX RPM		5400					
HZ	60//50	PH	3	CL	F	NOM.EFF.		84				
SER.F.	1.00	DES	B	SL HZ		1.7	WK2	0.06				
FRAME	143TC	RATING		40C AMB-CONT								
	55C AMB @ 1.0 SF											
	1.15 SF SINEWAVE						NEMA MG-1 PT 5,IP55					

AC Induction Motor Performance Data

Record # 76578

Typical performance - not guaranteed values

Winding: 35WGM760-R019		Type: 3520M	Enclosure: XPFC
Nameplate Data		380 V, 50 Hz: High Voltage Connection	
Rated Output (HP)	1.5	Full Load Torque	1.78 LB-FT
Volts	230/460//190/380	Start Configuration	direct on line
Full Load Amps	3.8/1.9//3.4/1.7	Breakdown Torque	8.7 LB-FT
R.P.M.	3500//2900	Pull-up Torque	3.69 LB-FT
Hz	60//50 Phase	Locked-rotor Torque	7.52 LB-FT
NEMA Design Code	B KVA Code	Starting Current	16.65 A
Service Factor (S.F.)	1	No-load Current	0.909 A
NEMA Nom. Eff.	84 Power Factor	Line-line Res. @ 25°C	9.66 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	34°C
		Locked-rotor Power Factor	61.4
		Rotor inertia	0.0553 LB-FT2

Load Characteristics 380 V, 50 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	62	75	83	87	89
Efficiency	65.1	77.1	80.7	82.1	82	81
Speed	2977	2958	2937	2915	2889	2862
Line amperes	0.981	1.15	1.37	1.65	1.96	2.34

ABB Motors and Mechanical Inc.

WINDING # 35WGM760

Typical performance - not guaranteed values.

1 HP 3 PH 50 HZ 2915 RPM 380 V 3520M

TORQUES (LB-FT): PO=8.7 PU=3.69 LR=7.52 LRA=16.65





