ABB BALDOR RELIANCE

Customer information packet

CDRX28324T-5

30HP, 3520RPM, 3PH, 60HZ, 286TSC, XPFC, F1
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 4:54:42 PM

Specifications

Enclosure	XPFC
Frame	286TSC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	26.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	26.0 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	J
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGZ218
Layout	10LYG898
Eff. date	06-11-2025
CD Diagram	CD0006
Poles	02
Leads	3#10
Proprietary	False
Created date	07-19-2019

IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1046M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	27.23 IN
Power Factor	90
Product Family	Hazardous Location Motor
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV											
NO.					**CC**	010A					
S/N					**TEMP CODE**	T3C					
SPEC.	10-0000-0935				**INV.TYPE**	PWM					
CAT.NO.	CDRX28324T-5				**C HP FR**	60	**C HP TO**	90			
HP	30				**CT HZ FROM**	6			**CT HZ TO**	60	
VOLTS	575				**VT HZ FROM**	6			**VT HZ TO**	60	
AMPS	26			**MAG CUR**	6.9						
RPM	3520			**MX RPM**	5400						
HZ	60	**PH**	3	**CL**	F	**NOM.EFF.**	91.7				
SER.F.	1.00	**DES**	B	**SL HZ**	1.3	**WK2**	1.98				
FRAME	286TSC	**RATING**	40C AMB-CONT								
	55C AMB @ 1.0 SF, 60C RISE										
	1.15SF ON SINEWAVE				NEMA MG-1 PT.5,IP55						

AC Induction Motor Performance Data
Record # 77475
Typical performance - not guaranteed values

Winding: 10WGZ218-R002	**Type:** 1046M	**Enclosure:** XPFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			30	**Full Load Torque**	44.4 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			26	**Breakdown Torque**	165 LB-FT
R.P.M.			3520	**Pull-up Torque**	59.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	78.3 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	175 A
Service Factor (S.F.)			1	**No-load Current**	6.89 A
NEMA Nom. Eff.	91.7	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.38 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
S.F. Amps				**Temp. Rise @ S.F. Load**	72°C
				Locked-rotor Power Factor	23.5
				Rotor inertia	1.97 LB-FT2

Load Characteristics 575 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	65	84	89	91	92	91
Efficiency	89.7	92.9	93.4	92.7	92.3	91.3
Speed	3580	3561	3543	3524	3502	3478
Line amperes	9.46	14.5	20.1	26.4	33.2	40.5


ABB Motors and Mechanical Inc.


WINDING # 10WGZ218

30 HP 3 PH 60 HZ 3520 RPM 575 V 1046M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=165 PU=59.5 LR=78.3 LRA=175





10LYG898
(1032-1060) = 27.24
13.74
3.00
.25
.38 KEY
1.88 LONG
Ø15.10
Ø11.23
Ø1.625
1.624
Ø10.500
10.497
SLINGER
DRAIN FITTING
HW4505A02
(EA. END)
8 HOLES
Ø.53
9.50
9.50
.88
11.00
4.76
12.75
15.39
16.53
7.58
PIPE PLUGS
(EA. END)
45°
45°
2.50
14.94
7.00 +.00 -.06
LEAD HOLE
1.50 NPT
HW3023E06
5.50
5.50
11.57
6.49
12.98
4 HOLES
.50-13 TAP ON
Ø9.00 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD MARKING FILE FOR STOCK PRODUCTS
REV: B
VERSION: 02
REVISED: 09:04:34 06/28/2023
TDR: 000001211833
MODEL NO. 10LYG898
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ XPFC 284-6TSC CL.I GP.C&D ONLY, DRILL RIG
10LYG898


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007			BALDOR - RELIANCE®
REV. LTR: E	VERSION: 01	TDR: 000001099922	
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0	3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED
MTL: –			SH 1 of 1