







TOLERANCE UNLESS OTHERWISE SHOWN:	
ONE PLACE DECIMAL	±0.1
TWO PLACE DECIMAL	±0.02
THREE PLACE DECIMAL	±0.003
ANGLE	±0°-30'
SURFACE FINISH	
250	



ENGR REF:

- D.E INNER SLINGER: 603284-001S
- O.D.E INNER SLINGER: 609158-001B

X/P PART PER U/L & MSHA. SEE RSP 3-0075-14-763-8	INSPECT

- SHAFT STD. PER 3425
- ▽ EXPLOSION PROOF SURFACE PER DWG. 402111-A

REV. DESC: ADDING XP NOTES			
REV: C	VERSION: 03	REVISED: 02:19:44 12/13/2022	TDR: 000001200416
MODEL NO. 609142-145			REF:
BY: USERWAL2	Material: FSCLI		B

1	CORE KEY	34180-070	GA	FS CLI	54.089
1	FINISHED SHAFT	3.12 X 32.33	A		
RA	NAME	SIZE OR CASTING	SYM	46024-	WT. (LB.)

BALDOR

E365T SHAFT 6313-6313 FCXP - CL1 GROUP C - INNER SLINGERS

BALDOR-DODGE-RELIANCE PROPRIETARY & CONFIDENTIAL:
THIS DRAWING IS THE PROPERTY OF BALDOR-DODGE-RELIANCE
AND/OR ITS SUBSIDIARIES AND IS NOT TO BE USED, DUPLICATED
OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION
OF THE COMPANY.

609142-145