

ABB BALDOR RELIANCE III

Customer information packet

CDRX18544T-5

5HP, 1750RPM, 3PH, 60HZ, 184TC, XPFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	184TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	5.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	5.3 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	C
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	06WGX200
Layout	06LYH515
Eff. date	01-19-2024
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	07-19-2019

IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.31 IN
Power Factor	79
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV													
NO.						CC	010A						
S/N						TEMP CODE				T3C			
SPEC.	06-0000-0181					INV.TYPE			PWM				
CAT.NO.	CDRX18544T-5					C HP FR		60	C HP TO		90		
HP	5					CT HZ FROM			6	CT HZ TO		60	
VOLTS	575					VT HZ FROM			6	VT HZ TO		60	
AMPS	5.3				MAG CUR		2.3						
RPM	1750				MX RPM		2700						
HZ	60	PH	3	CL	F	NOM.EFF.		89.5					
SER.F.	1.00	DES		B	SL HZ	1.7	WK2	0.39					
FRAME	184TC		RATING		40C AMB-CONT								
	55C AMB @ 1.0 SF												
	1.15 SF SINEWAVE					NEMA MG-1 PT 5,IP55							

AC Induction Motor Performance Data

Record # 77542

Typical performance - not guaranteed values

Winding: 06WGX200-R053			Type: 0642M		Enclosure: XPFC	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		5	Full Load Torque		15.04 LB-FT	
Volts		575	Start Configuration		direct on line	
Full Load Amps		5.3	Breakdown Torque		52.3 LB-FT	
R.P.M.		1750	Pull-up Torque		21.6 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		30.7 LB-FT
NEMA Design Code		B	KVA Code		J	
Service Factor (S.F.)		1	Starting Current		36.3 A	
NEMA Nom. Eff.		89.5	Power Factor		79	
Rating - Duty		40C	AMB-CONT			
			Line-line Res. @ 25°C		4.27 Ω	
			Temp. Rise @ Rated Load		54°C	
			Locked-rotor Power Factor		40.6	
			Rotor inertia		0.391 LB-FT ²	

Load Characteristics 575 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	64	76	81	84	85
Efficiency	85.2	89.8	90.1	89.7	88.2	86.4
Speed	1788	1777	1764	1751	1736	1719
Line amperes	2.61	3.26	4.13	5.14	6.31	7.59


ABB Motors and Mechanical Inc.


WINDING # 06WGX200

Typical performance - not guaranteed values.




5 HP 3 PH 60 HZ 1750 RPM 575 V 0642M

TORQUES (LB-FT): PO=52.3 PU=21.6 LR=30.7 LRA=36.3





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1