

ABB BALDOR RELIANCE III

Customer information packet

CDRX251524T-5

15HP, 3530RPM, 3PH, 60HZ, 254TC, XPFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	254TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	13.700 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	13.7 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGT021
Layout	09LYF368
Eff. date	02-14-2024
CD Diagram	CD0006
Poles	02
Leads	3#12
Proprietary	False
Created date	07-19-2019

IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0934M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	26.00 IN
Power Factor	88
Product Family	Hazardous Location Motor
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3530 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV														
NO.						CC	010A							
S/N						TEMP CODE				T3C				
SPEC.	09-0000-1601					INV.TYPE				PWM				
CAT.NO.	CDRX251524T-5					C HP FR		60	C HP TO		90			
HP	15					CT HZ FROM			6	CT HZ TO			60	
VOLTS	575					VT HZ FROM			6	VT HZ TO			60	
AMPS	13.7				MAG CUR		4.5							
RPM	3530				MX RPM		5400							
HZ	60	PH	3	CL	F	NOM.EFF.		91						
SER.F.	1.00	DES		A	SL HZ		1.2	WK2		0.87				
FRAME	254TC		RATING		40C AMB-CONT									
	55C AMB @ 1.0 SF, 60C RISE													
	1.15SF ON SINEWAVE					NEMA MG-1 PT.5,IP55								

AC Induction Motor Performance Data

Record # 77607

Typical performance - not guaranteed values

Winding: 09WGT021-R003			Type: 0934M		Enclosure: XPFC			
Nameplate Data			575 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		15	Full Load Torque		22.2 LB-FT			
Volts		575	Start Configuration		direct on line			
Full Load Amps		13.7	Breakdown Torque		97.9 LB-FT			
R.P.M.		3530	Pull-up Torque		31.5 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		39.1 LB-FT		
NEMA Design Code		A	KVA Code	H	Starting Current		98.1 A	
Service Factor (S.F.)		1	No-load Current		4.45 A			
NEMA Nom. Eff.		91	Power Factor		88	Line-line Res. @ 25°C		0.949 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		56°C		
S.F. Amps				Temp. Rise @ S.F. Load		70°C		
				Locked-rotor Power Factor		29.2		
				Rotor inertia		0.868 LB-FT2		

Load Characteristics 575 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	59	79	87	89	90	90
Efficiency	86.4	91.3	91.5	91.5	91.1	90.2
Speed	3582	3566	3548	3530	3511	3489
Line amperes	5.55	7.87	10.6	13.7	16.9	20.5


ABB Motors and Mechanical Inc.


WINDING # 09WGT021

Typical performance - not guaranteed values.



15 HP 3 PH 60 HZ 3530 RPM 575 V 0934M

TORQUES (LB-FT) : PO=97.9 PU=31.5 LR=39.1 LRA=98.1





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1