



Customer information packet

CECP2333T-4

15HP, 1765RPM, 3PH, 60HZ, 254TC, 0944M, TEFC, F

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	254TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.2
Current @ Voltage	18.100 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part detail

Revision	AF
Type	AC
Mech. spec.	09H180
Base	
Status	PRD/A
Elec. spec.	09WGZ914
Layout	09LYH180
Eff. date	11-14-2023
CD Diagram	CD0006
Poles	04
Leads	3#12
Proprietary	False
Created date	11-29-2012

Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	18.1 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	25.28 IN
Power Factor	83
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3995ABBL

CAT #	CECP2333T-4			SER		CC	010A						
SPEC	09H180Z914			RATING	40C AMB-CONT								
HZ	VOLTS			AMPS	RPM	HP	CODE	SF	DES	PF	NEMA NOM. EFF		
60	460			18.1	1765	15	H	1.15	A	83 %	92.4 %		
										%		%	
PH	3	CL	F	MAX RPM	2700	MAX CORR KVAR		USABLE AT 208V		N/A			
IP55	FR	254TC	ENCL	TEFC	DE BRG	6309	ODE BRG	6309					
GREASE	POLYREX EM					MTR WT	314	LBS					
USABLE AT	50HZ 10HP 380V 15.3A					SF1.0							
CL I DIV 2 GRPS A,B,C,D				CL I ZONE 2 GRPS				IIA,IIB,IIC		TEMP T	160	C	
1.0 SF ON PWM INVERTER			POWER	INV TEMP CL		180	C						
CHP	60-90	HZ	1.5:1	CT	1.2-60	HZ	50:1	VT	0-60	HZ	1000:1		
SPACE HEATER LEADS H1-H2:				TIE LIKE NUMBERS				TOGETHER					
V		A		W		MAX SPACE HEATER TEMP							

AC Induction Motor Performance Data

Record # 47166

Typical performance - not guaranteed values

Winding: 09WGX914-R021		Type: 0944M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		15	Full Load Torque		44.5 LB-FT
Volts		460	Start Configuration		direct on line
Full Load Amps		18.1	Breakdown Torque		153 LB-FT
R.P.M.		1765	Pull-up Torque		69.5 LB-FT
Hz	60 Phase	3	Locked-rotor Torque		86.5 LB-FT
NEMA Design Code	A KVA Code	H	Starting Current		127 A
Service Factor (S.F.)		1.15	No-load Current		7.56 A
NEMA Nom. Eff.	92.4 Power Factor	83	Line-line Res. @ 25°C		0.59555 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		54°C
S.F. Amps			Temp. Rise @ S.F. Load		67°C
			Locked-rotor Power Factor		33.1
			Rotor inertia		1.92 LB-FT ²

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	69	79	83	85	87	84
Efficiency	88.2	92.2	92.7	92.4	91.5	90.4	91.9
Speed	1791.3	1783.1	1774	1765.2	1754.6	1743.1	1759
Line amperes	8.62	11	14.5	18.2	22.6	26.9	20.8


ABB Motors and Mechanical Inc.

WINDING # 09WGZ914

15 HP 3 PH 60 HZ 1765 RPM 460 V 0944M



Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=153 PU=69.5 LR=86.5 LRA=127



8/15/2024 ACPERF, record # 47166

CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -		© □

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1