

ABB BALDOR RELIANCE III

Customer information packet

CECP3587T-5

2HP, 1765RPM, 3PH, 60HZ, 145TC, 0528M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T4
Heater Indicator	No Heater

Part Detail

Revision	C
Type	AC
Mech. spec.	05F007
Base	
Status	PRD/A
Elec. spec.	05WGX552
Layout	05LYF007
Eff. date	08-25-2026
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	12-20-2023

High Voltage Full Load Amps	2.3 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.38 IN
Power Factor	75
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3257									
CAT.NO.	CECP3587T-5								
SPEC.	05F007X552G1								
HP	2 TE								
VOLTS	575								
AMP	2.3								
RPM	1765								
FRAME	145TC	HZ		60	PH		3		
SER.F.	1.15	CODE	L	DES	B	CL	F		
RATING	40C AMB-CONT								
SN									
DE	6205	ODE		6205					
NEMA-NOM-EFF	86.5	PF	75						
G.MIN.EFF	86.5	CC	010A						
T. CODE	T4	T=	135						

NP3260			
SPEC.	05F007X552G1		
D.E. BRG.	25BC02XP30X		
O.D.E. BRG.	25BC02XP30X		
GREASE	POLYREX EM		
RPM MAX		MAX. KVAR	
BLANK	SFA 2.6		
INV.TYPE			
T=			
C HP FR	C HP TO		
CT HZ FROM	CT HZ TO		
VT HZ FROM	VT HZ TO		
HTR-VOLTS	HTR-AMPS		
HTR-WATTS	MAX. SPACE HEATER TEMP.		

AC Induction Motor Performance Data

Record # 98658

Typical performance - not guaranteed values

Winding: 05WGX552-R006			Type: 0528M		Enclosure: TEFC	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		2	Full Load Torque		5.96 LB-FT	
Volts		575	Start Configuration		direct on line	
Full Load Amps		2.3	Breakdown Torque		24.3 LB-FT	
R.P.M.		1765	Pull-up Torque		12 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque	16.2 LB-FT	
NEMA Design Code	B	KVA Code	L	Starting Current	18.9 A	
Service Factor (S.F.)		1.15	No-load Current		1.46 A	
NEMA Nom. Eff.	86.5	Power Factor	75	Line-line Res. @ 25°C	15.5 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		41°C	
S.F. Amps		2.6	Temp. Rise @ S.F. Load		50°C	
			Locked-rotor Power Factor		57	
			Rotor inertia		0.202 lb-ft²	

Load Characteristics 575 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	53	66	75	80	83	78
Efficiency	76	84	86	86	86	84	86
Speed	1790	1782	1773	1763	1753	1741	1757
Line amperes	1.5	1.68	1.97	2.32	2.74	3.21	2.57


ABB Motors and Mechanical Inc.


WINDING # 05WGX552

Typical performance - not guaranteed values.




2 HP 3 PH 60 HZ 1765 RPM 575 V 0528M

TORQUES (LB-FT): PO=24.3 PU=12 LR=16.2 LRA=18.9





CD0006



- NOTES:
1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10: 24: 49 02/19/2019	BY: ENBRIRO
MTL: —		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1