ABB BALDOR RELIANCE

Customer information packet

CECP3768T

5HP, 1160RPM, 3PH, 60HZ, 215TC, 0748M, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/2/2026 2:36:18 AM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	2
Current @ Voltage	7.300 A @ 460.0 V
	14.600 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features

Part Detail

Revision	M
Type	AC
Mech. spec.	07K373
Base	
Status	PRD/A
Elec. spec.	07WGX823
Layout	07LYK373
Eff. date	09-14-2022
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	11-18-2013

Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	7.3 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	20.24 IN
Power Factor	72
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1160 rpm
Speed Code	Single Speed

Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3257								
CAT.NO.	CECP3768T							
SPEC.	07K373X823G4							
HP	5 TE							
VOLTS	230/460							
AMP	14.6/7.3							
RPM	1160							
FRAME	215TC	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	K	**DES**	A	**CL**	F	
RATING	40C AMB-CONT							
SN								
DE	6307	**ODE**	6307					
NEMA-NOM-EFF	90.2	**PF**	72					
G.MIN.EFF	88.5	**CC**	010A					
T. CODE	T3C	**T=**	160					

NP3260					
SPEC.	07K373X823G4				
D.E. BRG.	35BC03XP30X				
O.D.E. BRG.	35BC03XP30X				
GREASE	POLYREX EM				
RPM MAX	1800	**MAX. KVAR**	N/A		
BLANK					
INV.TYPE	PWM				
T=	160				
C HP FR	60	**C HP TO**	90		
CT HZ FROM	2	**CT HZ TO**	60		
VT HZ FROM	-0	**VT HZ TO**	60		
HTR-VOLTS		**HTR-AMPS**			
HTR-WATTS		**MAX. SPACE HEATER TEMP.**			

AC Induction Motor Performance Data
Record # 47060
Typical performance - not guaranteed values

Winding: 07WGX823-R030	**Type:** 0748M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	22.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			14.6/7.3	**Breakdown Torque**	77.4 LB-FT
R.P.M.			1160	**Pull-up Torque**	46.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	56.1 LB-FT
NEMA Design Code	A	**KVA Code**	K	**Starting Current**	51.9 A
Service Factor (S.F.)			1.15	**No-load Current**	3.7 A
NEMA Nom. Eff.	90.2	**Power Factor**	72	**Line-line Res. @ 25ºC**	1.58 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	50°C
S.F. Amps				**Temp. Rise @ S.F. Load**	62°C
				Rotor inertia	1.19 LB-FT2

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	34	54	65	72	75	76	74
Efficiency	86.2	90.3	91	90.5	89.3	87.7	89.8
Speed	1190	1181	1173	1163	1151	1138	1156
Line amperes	4.01	4.79	5.88	7.29	8.77	10.44	8.18


ABB Motors and Mechanical Inc.


WINDING # 07WGX823

5 HP 3 PH 60 HZ 1160 RPM 460 V 0748M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=77.4 PU=46.7 LR=56.1 LRA=51.9




07LYK373
717-750 = 20.23
9.11
3.12
.26
PLUG
GREASE FITTING W/ CAP (EA. END)
Ø12.19
.31 KEY 2.38 LONG
Ø 8.500 8.497
9.06
Ø 1.3750 1.3745
SLINGER
GROUND LUG
8 HOLES Ø.41
GREASE RELIEF (EA. END)
DRAIN FITTING (EA. END)
5.50
.57
5.50
4.24
7.00
8.13
14.65
8.90
5.75
2.04
45°
45°
5.74
5.25
5.19
LEAD HOLE 1.00 N.P.T.
4 HOLES .50-13 TAP ON Ø7.25 B.C.
4.25
4.25
7.25
4.82
9.63
OMIT LOCKWASHER & USE SEALER UNDER SCREW HEADS
FORSHEDA SLINGER
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: REMOVE GROUND LUG ON F2 SIDE
REV: F
VERSION: 06
REVISED: 03:50:30 06/09/2025
TDR: 000001257717
MODEL NO. 07LYK373
REF: -
BY: ENBILT0
B
BALDOR - RELIANCE®
STD HORZ 213-5TC TEFC M CP W/6307 BRGS, LIPPED LID
07LYK373

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS