ABB BALDOR RELIANCE

Customer information packet

CECP3582T

1HP, 1170RPM, 3PH, 60HZ, 145TC, 0526M, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 11:17:36 AM

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	2
Current @ Voltage	3.600 A @ 208.0 V
	3.560 A @ 230.0 V
	1.780 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %

Part Detail

Revision	C
Type	AC
Mech. spec.	05F144
Base	
Status	PRD/A
Elec. spec.	05WGX907
Layout	05LYF144
Eff. date	03-19-2026
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	09-09-2022

Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T4
Heater Indicator	No Heater
High Voltage Full Load Amps	1.8 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0526M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	13.38 IN
Power Factor	64
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3258									
CAT.NO.	CECP3582T								
SPEC.	05F144X907G1								
HP	1 TE								
VOLTS	208-230/460								
AMP	3.6-3.56/1.78								
RPM	1170								
FRAME	145TC	**HZ**	60		**PH**	3			
SER.F.	1.15	**CODE**	J	**DES**	B		**CL**	F	
RATING	40C AMB-CONT								
SN									
DE	6205	**ODE**	6205						
NEMA-NOM-EFF	82.5	**PF**	64						
G.MIN.EFF	80	**CC**	010A						
T. CODE	T4	**T=**	135						

NP3261					
SPEC.	05F144X907G1				
D.E. BRG.	25BC02XP30X				
O.D.E. BRG.	25BC02XP30X				
GREASE	POLYREX EM				
RPM MAX	1800	**MAX. KVAR**	0.66		
BLANK	SFA 4-3.9/1.95				
INV.TYPE	PWM				
T=	135				
C HP FR	60	**C HP TO**	90		
CT HZ FROM	2	**CT HZ TO**	60		
VT HZ FROM	-0	**VT HZ TO**	60		
HTR-VOLTS		**HTR-AMPS**			
HTR-WATTS		**MAX. SPACE HEATER TEMP.**		56C	


AC Induction Motor Performance Data
Record # 87637
Typical performance - not guaranteed values


Winding: 05WGX907-R001	**Type:** 0526M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	4.47 LB-FT
Volts			208-230/460	**Start Configuration**	direct on line
Full Load Amps			3.6-3.56/1.78	**Breakdown Torque**	13.22 LB-FT
R.P.M.			1170	**Pull-up Torque**	7.94 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	9.7 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	10.19 A
Service Factor (S.F.)			1.15	**No-load Current**	1.19 A
NEMA Nom. Eff.	82.5	**Power Factor**	64	**Line-line Res. @ 25ºC**	19.9 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	48°C
S.F. Amps			4-3.9/1.95	**Temp. Rise @ S.F. Load**	57°C
				Locked-rotor Power Factor	50.1
				Rotor inertia	0.189 lb-ft²


Load Characteristics 460 V, 60 Hz, 1 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	27	43	55	64	70	73	68
Efficiency	70.2	80.1	82.3	82.5	81.5	79.4	81.9
Speed	1193	1187	1180	1172	1163	1153	1167
Line amperes	1.23	1.36	1.54	1.78	2.06	2.41	1.95


ABB Motors and Mechanical Inc.
WINDING # 05WGX907
Typical performance - not guaranteed values.
1 HP 3 PH 60 HZ 1170 RPM 460 V 0526M
TORQUES(LB-FT): PO=13.22 PU=7.94 LR=9.7 LRA=10.19
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF
%PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1 HP)
11/15/2026 ACPERF, record # 87637


05LYF144
(510-535) = 13.38
5.88
2.12
.13
.13
PLUG
GREASE FITTING
W/CAP (EA. END)
NAMEPLATE
.19 KEY
1.38 LONG
Ø8.00
Ø4.500
4.497
Ø6.48
Ø.8750
.8745
SLINGER
FORSHEDA
SLINGER
GROUND
LUG
8 HOLES
Ø.38
4.00
.44
4.00
2.75
5.00
5.88
GREASE RELIEF
(EA. END)
DRAIN FITTING
(EA. END)
10.42
6.42
4.00
1.95
45°
45°
4.01
3.50
3.44
4 HOLES
.38-16 TAP ON
Ø5.88 B.C.
LEAD HOLE
.75 N.P.T.
2.75
2.75
5.07
6.65
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOADING OF SWD DWG FOR 2D TO 3D CONVERSION - PKG17
REV: C
VERSION: 03
REVISED: 10:29:52 02/08/2019
TDR: 000001098865
MODEL NO. 05LYF144
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
HORZ 143-5T TEFC M CP W/6205 BRGS (EACH END), GRSRS/RLFS
SH 1 of 1
05LYF144

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS