ABB BALDOR RELIANCE

Customer information packet

CECP3660T

3HP, 3500RPM, 3PH, 60HZ, 182TC, 0628M, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/22/2026 11:38:11 AM

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	7.500 A @ 208.0 V
	6.800 A @ 230.0 V
	3.400 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	V
Type	AC
Mech. spec.	06H482
Base	
Status	PRD/A
Elec. spec.	06WGW036
Layout	06LYH482
Eff. date	11-11-2020
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	05-13-2010

Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.4 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0628M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	16.68 IN
Power Factor	92
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3500 rpm

Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3257								
CAT.NO.	CECP3660T							
SPEC.	06H482W036G2							
HP	3 TE							
VOLTS	230/460							
AMP	6.8/3.4							
RPM	3500							
FRAME	182TC	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	L	**DES**	B	**CL**	F	
RATING	40C AMB-CONT							
SN								
DE	6206	**ODE**	6206					
NEMA-NOM-EFF	88.5	**PF**	92					
G.MIN.EFF	86.5	**CC**	010A					
T. CODE	T3C	**T=**	160					

NP3260					
SPEC.	06H482W036G2				
D.E. BRG.	30BC02XP30X				
O.D.E. BRG.	30BC02XP30X				
GREASE	POLYREX EM				
RPM MAX	5400	**MAX. KVAR**	N/A		
BLANK					
INV.TYPE	PWM				
T=	160				
C HP FR	60	**C HP TO**	90		
CT HZ FROM	6	**CT HZ TO**	60		
VT HZ FROM	3	**VT HZ TO**	60		
HTR-VOLTS		**HTR-AMPS**			
HTR-WATTS		**MAX. SPACE HEATER TEMP.**			

AC Induction Motor Performance Data
Record # 47052
Typical performance - not guaranteed values

Winding: 06WGW036-R021	**Type:** 0628M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			3	**Full Load Torque**	4.5 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			6.8/3.4	**Breakdown Torque**	23.3 LB-FT
R.P.M.			3500	**Pull-up Torque**	15.2 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	16 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	32 A
Service Factor (S.F.)			1.15	**No-load Current**	1.06 A
NEMA Nom. Eff.	88.5	**Power Factor**	92	**Line-line Res. @ 25ºC**	4.1 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	32°C
S.F. Amps				**Temp. Rise @ S.F. Load**	39°C
				Locked-rotor Power Factor	44.2
				Rotor inertia	0.126 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	64	83	90	93	95	99	93
Efficiency	81.2	87.5	89.2	89.3	88.9	88.2	89.1
Speed	3577	3556	3534	3509	3487	3467	3500
Line amperes	1.39	1.96	2.66	3.4	4.12	4.79	3.83


ABB Motors and Mechanical Inc.


WINDING # 06WGW036

3 HP 3 PH 60 HZ 3500 RPM 460 V 0628M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=23.3 PU=15.2 LR=16 LRA=32




06LYH482
614 - 643 = 16.68
7.67
AUXILIARY NAMEPLATE (WHEN REQ'D)
PLUG
GREASE FITTING W/CAP (EA. END)
.25
2.62
NAMEPLATE
2.75
.25 KEY 1.75 LONG
SLINGER
8.86
Ø 8.500 8.497
Ø 1.1250 1.1245
FORSHEDA SLINGER
GROUND LUG
8 HOLES Ø.41
4.50
.49
4.50
3.50
6.50
GREASE RELIEF (EACH END)
DRAIN FITTING (EACH END)
11.92
7.18
4.73
45°
45°
2.04
11.29
4.50 +.06 -.00
LEAD HOLE .75 N.P.T.
4 HOLES .50-13 TAP ON Ø7.25 B.C.
3.75
3.75
5.82
4.31
8.62
OMIT LOCKWASHER & USE SEALER UNDER RETAINER SCREW HEAD
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: SHOVE ADD NP WHEN REQ'D
REV: E
VERSION: 05
REVISED: 08:55:38 10/09/2020
TDR: 000001150783
MODEL NO. 06LYH482
REF: -
BY: USFRHAR
B
BALDOR - RELIANCE®
STD HORZ 182-4TC TEFC M CP W/6206 BRGS, LIPPED KOBX LID
06LYH482

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS