

ABB BALDOR RELIANCE III

Customer information packet

CECP83764T-4

3HP, 1165RPM, 3PH, 60HZ, 213TC, 0736M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	213TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.7
Current @ Voltage	4.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	W
Type	AC
Mech. spec.	07M320
Base	
Status	PRD/A
Elec. spec.	07WGX816
Layout	07LYM320
Eff. date	08-04-2022
CD Diagram	CD0006
Poles	06
Leads	3#14
Proprietary	False
Created date	11-18-2013

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	4.5 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Ring Terminals
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	20.23 IN
Power Factor	70
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4328									
CAT.NO.	CECP83764T-4								
SPEC.	07M320X816G2								
HP	3 TE				IP	56			
VOLTS	460								
AMPS	4.5								
R.P.M.	1165								
FRAME	213TC		HZ		60		PH	3	
SER.F.	1.15	CODE	K	DES.	B	CLASS		F	
RATING	40C AMB-CONT								
SN									
DE	6307		ODE		6307				
NEMA NOM. EFF.	89.5		P.F.		70				
GUAR. MIN. EFF.	87.5		CC		010A				
T. CODE	T3C		TEMP=		160				

NP3186					
SPEC.	07M320X816G2				
ABMA DE BRG	35BC03X30X				
ABMA ODE BRG	35BC03X30X				
GREASE	POLYREX EM				
MOTOR WEIGHT	211	ROTOR BARS	27	STATOR BARS	36
MAX. R.P.M.	1800	MAX. KVAR	1.34		
INV.TYPE	PWM				
T=	160				
CHP	60	TO	90		
CT	1.7	TO	60		
VT	-0	TO	60		
HTR-VOLTS	N/A	HTR-AMPS	N/A		
HTR-WATTS		MAX. SPACE HEATER TEMP.	N/A		

AC Induction Motor Performance Data

Record # 92665

Typical performance - not guaranteed values

Winding: 07WGX816-R019				Type: 0736M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		3		Full Load Torque		13.5 LB-FT	
Volts		460		Start Configuration		direct on line	
Full Load Amps		4.5		Breakdown Torque		48.9 LB-FT	
R.P.M.		1165		Pull-up Torque		23 LB-FT	
Hz		60		Phase		3	
NEMA Design Code		B		KVA Code		K	
Service Factor (S.F.)		1.15		No-load Current		2.39 A	
NEMA Nom. Eff.		89.5		Power Factor		70	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps						Temp. Rise @ S.F. Load	
						Locked-rotor Power Factor	
						Rotor inertia	

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	34	53	64	70	74	75	72
Efficiency	82.2	88.3	89.3	89.8	88.7	87.5	89.3
Speed	1193	1186	1178	1170	1159	1148	1163
Line amperes	2.58	3.07	3.72	4.46	5.35	6.37	4.99


ABB Motors and Mechanical Inc.


WINDING # 07WGX816

Typical performance - not guaranteed values.




3 HP 3 PH 60 HZ 1165 RPM 460 V 0736M

TORQUES (LB-FT): PO=48.9 PU=23 LR=30 LRA=31.5





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10: 24: 49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1