ABB BALDOR RELIANCE

Customer information packet

CECR9604T

60HP, 1785RPM, 3PH, 60HZ, 364TC, A3662M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 9:13:29 PM

Specifications

Enclosure	TEFC
Frame	364TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM
	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	142.000 A @ 230.0 V
	71.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	71.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Max Speed	2700 rpm

Part Detail

Revision	-
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4074
Layout	617428-136
Eff. date	07-24-2025
CD Diagram	416820-002
Poles	04
Leads	3#4,6#6
Proprietary	False
Created date	07-23-2025

Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A3662M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.48 IN
Power Factor	83
Product Family	Crusher Duty
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.25
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1785 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3980LUA

CAT #	CECR9604T			**SER**				**CC**	010A															
SPEC	A36-9187-4074			**RATING**	40C AMB-CONT																			
HZ	**VOLTS**			**AMPS**			**RPM**	**HP**	**CODE**		**SF**	**DES**	**PF**		**NEMA NOM. EFF**									
60	230/460			142/71			1785	60	H		1.25	A	83	%	95	%								
	-													%		%								
PH	3	**CL**	F	**MAX CORR KVAR**	17																			
BRG	**DE**	6313		**ODE**	6313		**ENCL**	TEFC		**FR**	364TC			55										
GREASE	POLYREX EM									**MTR WT**	910	**LBS**												
USABLE AT	50HZ 50HP 190/380V 144/72A									SF1.0														
INV READY	**1.0 SF VPWM**		**CT**	10-60	**HZ**	6:1	**VT**	0-60	**HZ**	1000:1	**CHP**	60-90	**HZ**	1.5:1										
MAX RPM	2700	SFA 178/89																						

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-136


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


E365TC/E364TC MOUNTING HOLES

COOLING: FAN COOLED









DIMENSIONS ARE IN INCHES.
WEIGHT =900 LBS +/- 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER 1 OF 2

617428-136

FACE & ECCENTRICITY RUNOUT = .007 T.I.R. MAX.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

REV. DESC: NEW DRW			
REV: C	VERSION: 03	REVISED: 10:20:38 10/07/2022	TDR: 000001197796
MODEL NO. 617428-136			
BY: USJEDIL			C

BALDOR

E365/364TC TEFC F1 FOOT/CAST IRON BOX

617428-136

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-136


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


E365TC/E364TC MOUNTING HOLES

COOLING: FAN COOLED









DIMENSIONS ARE IN MILLIMETERS.
WEIGHT = 408 LBS +/- 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER 2 OF 2

617428-136

FACE & ECCENTRICITY RUNOUT = .18 T.I.R. MAX.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

REV. DESC: NEW DRW			
REV: C	VERSION: 03	REVISED: 10:20:38 10/07/2022	TDR: 000001197796
MODEL NO. 617428-136			
BY: USJEDIL			C


BALDOR


E365/364TC TEFC F1 FOOT/CAST IRON BOX

617428-136

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002