ABB BALDOR RELIANCE

Customer information packet

CECP83582T-4

1HP, 1155RPM, 3PH, 60HZ, 145TC, 0526M, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/22/2026 11:30:21 AM

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	2.0
Current @ Voltage	1.700 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	C
Type	AC
Mech. spec.	05EE943
Base	
Status	PRD/A
Elec. spec.	05WGX572
Layout	05LYEE943
Eff. date	11-08-2023
CD Diagram	CD0006
Poles	06
Leads	3#18
Proprietary	False
Created date	09-09-2022

Haz Area Temp Code	T4
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0526M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	13.38 IN
Power Factor	67
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1155 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP4328								
CAT.NO.	CECP83582T-4							
SPEC.	05EE943X572G1							
HP	1 TE		**IP**	56				
VOLTS	460							
AMPS	1.7							
R.P.M.	1155							
FRAME	145TC	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	J	**DES.**	B	**CLASS**	F	
RATING	40C AMB-CONT							
SN								
DE	6205	**ODE**	6205					
NEMA NOM. EFF.	82.5	**P.F.**	67					
GUAR. MIN. EFF.	80	**CC**	010A					
T. CODE	T4	**TEMP=**	135					

NP3186							
SPEC.	05EE943X572G1						
ABMA DE BRG	25BC02X30X						
ABMA ODE BRG	25BC02X30X						
GREASE	POLYREX EM						
MOTOR WEIGHT	61	**ROTOR BARS**	27	**STATOR BARS**	36		
MAX. R.P.M.	1800	**MAX. KVAR**					
	SFA 1.86						
INV.TYPE	PWM						
T=	135						
CHP	60	**TO**	90				
CT	2.0	**TO**	60				
VT	-0	**TO**	60				
HTR-VOLTS	N/A	**HTR-AMPS**	N/A				
HTR-WATTS		**MAX. SPACE HEATER TEMP.**			N/A		

AC Induction Motor Performance Data
Record # 82314
Typical performance - not guaranteed values

Winding: 05WGX572-R001	**Type:** 0526M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			1	**Full Load Torque**	4.48 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			1.7	**Breakdown Torque**	11.9 LB-FT
R.P.M.			1155	**Pull-up Torque**	7.06 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	8.62 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	9.06 A
Service Factor (S.F.)			1.15	**No-load Current**	1.02 A
NEMA Nom. Eff.	82.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	21.1 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	46°C
S.F. Amps				**Temp. Rise @ S.F. Load**	56°C
				Locked-rotor Power Factor	48.3
				Rotor inertia	0.189 lb-ft²

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	47	59	67	72	75	70
Efficiency	73.6	81.7	83.5	83.2	81.6	79.1	82.2
Speed	1193	1185	1178	1169	1159	1147	1163
Line amperes	1.07	1.21	1.41	1.67	1.98	2.35	1.86


ABB Motors and Mechanical Inc.

WINDING # 05WGX572

1 HP 3 PH 60 HZ 1155 RPM 460 V 0526M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=11.9 PU=7.06 LR=8.62 LRA=9.06



AC Induction Motor Performance Data
Record # 99230
Typical performance - not guaranteed values


Winding: 05WGX572-R001	**Type:** 0526M	**Enclosure:** TEFC

Nameplate Data				**368 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			1	**Full Load Torque**	4.56 LB-FT
Volts			368	**Start Configuration**	direct on line
Full Load Amps			1.7	**Breakdown Torque**	7.6 LB-FT
R.P.M.			1155	**Pull-up Torque**	4.4 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	5.4 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	7.2 A
Service Factor (S.F.)			1.15	**No-load Current**	0.79 A
NEMA Nom. Eff.	82.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	21.1 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	57°C
S.F. Amps			1.86	**Temp. Rise @ S.F. Load**	78°C
				Locked-rotor Power Factor	48.3
				Rotor inertia	0.189 lb-ft²

Load Characteristics 368 V, 60 Hz, 1 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	41	61	71	75	76	69	76
Efficiency	79.8	84	83.2	80.5	75.7	59.7	77.6
Speed	1189	1177	1165	1149	1125	1033	1135
Line amperes	0.88	1.13	1.48	1.93	2.52	4.09	2.28



ABB Motors and Mechanical Inc.
WINDING # 05WGX572
Typical performance - not guaranteed values.
1 HP 3 PH 60 HZ 1155 RPM 368 V 0526M
TORQUES(LB-FT): PO=7.6 PU=4.4 LR=5.4 LRA=7.2
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF
%PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1 HP)
11/22/2026 ACPERF, record # 99230


05LYEE943
13.38
5.88
2.10
.13
.13
GREASE FITTING WITH CAPS (EACH END)
.19 KEY 1.38 LONG
8.00 DIA.
INPRO SEAL (EA. END)
GND LUG (EACH SIDE)
8 HOLES .38 DIA.
4.00
4.00
2.75
5.00
.44
5.88
FORSHEDA SLINGER (INSIDE) BOTH ENDS
GREASE RELIEF (EACH END)
⌀4.500 4.497
⌀.8750 .8745
.001 A
⌀6.48
7.48
6.01
3.50 +.00 -.06
.005
A
10.89
6.89
4.00
45°
45°
2.75
2.75
5.31
3.26
6.51
LEAD HOLE 1.00 N.P.T.
DRAIN FITTING (EA. END)
4 HOLES .38-16 TAP ON 5.88 DIA. B.C.
FRONT END DETAIL
PULLEY END DETAIL
REV. DESC: ADD '1.00 N.P.T. LEAD HOLE' TO DRWG DESC
REV: A
VERSION: 01
REVISED: 02:29:11 12/01/2015
TDR: 000000955500
MODEL NO. 05LYEE943
REF:
BY: ENKANV0
B
BALDOR ELECTRIC Co.
HOR 143-5TC TEFC 05M IEEE841 LOCKED PU.BRG,INPROS & 1.00 NPT
05LYEE943


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1