

ABB BALDOR RELIANCE III

Customer information packet

CEFWWDM3546

1HP, 1770RPM, 3PH, 60HZ, 56C, 3522M, TEFC, F1, N

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.400 A @ 230.0 V 3.300 A @ 208.0 V 3.200 A @ 208.0 V 1.700 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	F
Type	AC
Mech. spec.	35E1679
Base	
Status	PRD/A
Elec. spec.	35WGZ805
Layout	35LYE1679
Eff. date	05-13-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3522M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.35 IN
Power Factor	69
Product Family	Super White Washdown
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP1669L											
CAT.NO.	CEFWWDM3546										
SPEC.	35E1679Z805G1										
HP	1										
VOLTS	208-230/460										
AMP	3.3-3.4/1.7										
RPM	1770										
FRAME	56C		HZ	60				PH	3		
SER.F.	1.15	CODE	N	DES	B	CLASS		F			
NEMA-NOM-EFF	85.5	PF	66								
RATING	40C AMB-CONT										
CC	010A										
DE	6205		ODE	6205							
ENCL	TEFC	SN									
BLANK	SFA 3.6/1.8										

AC Induction Motor Performance Data

Record # 105401

Typical performance - not guaranteed values

Winding: 35WGZ805-R001			Type: 3522M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1	Full Load Torque		2.97 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		3.3-3.4/1.7	Breakdown Torque		14.7 LB-FT		
R.P.M.		1770	Pull-up Torque		7.5 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		9.4 LB-FT	
NEMA Design Code		B	KVA Code		N		
Service Factor (S.F.)		1.15	Starting Current		15.6 A		
NEMA Nom. Eff.		85.5	Power Factor		66		
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		37°C
S.F. Amps		3.6/1.8	Temp. Rise @ S.F. Load		43°C		
			Locked-rotor Power Factor		58.6		
			Rotor inertia		0.159 lb-ft²		

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	44	57	66	73	78	70
Efficiency	71.1	81.8	85.2	86.5	86.6	86.3	86.6
Speed	1796	1790	1784	1778	1772	1765	1774
Line amperes	1.23	1.31	1.46	1.64	1.86	2.09	1.77

ABB Motors and Mechanical Inc.

WINDING # 35WGZ805

Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 1770 RPM 460 V 3522M

TORQUES (LB-FT): PO=14.7 PU=7.5 LR=9.4 LRA=15.6





