

ABB BALDOR RELIANCE III

Customer information packet

CECP84104T-5

30HP, 1770RPM, 3PH, 60HZ, 286TC, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	286TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	30
Current @ Voltage	28.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3

Part Detail

Revision	M
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGZ479
Layout	10LY-000-170
Eff. date	09-26-2025
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	01-23-2019

Heater Indicator	No Heater
High Voltage Full Load Amps	28.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP56
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Ring Terminals
Motor Standards	NEMA
Motor Type	1060M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	28.00 IN
Power Factor	84
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate
NP4332

CAT.NO.	CECP84104T-5			P/N			ENCLOSURE			TEFC				
SPEC.	10-0000-0474			CC	010A	FRAME	286TC	S/N						
HP	30			CLASS	F	HZ	60	ODE BRG	6311	DE BRG	6311			
RPM	1770	RPM MAX	2700	PH	3	DES	B	D.E. BRG.	55BC03X30X					
VOLT	575			KVA-CODE	G		O.D.E. BRG.		55BC03X30X					
AMP	28			MOTOR WEIGHT			487	GREASE	POLYREX EM					
RATING	40C AMB-CONT			MAX. KVAR			7.4	BLANK						
NEMA-NOM-EFF	93.6	# OF ROTOR BARS			40	SER.F.	1.15	IP	56					
G.MIN.EFF	92.4	# OF STATOR SLOTS			48	PF	84	INV.TYPE	PWM					
TEMP CODE	T3	INVERTER-TEMP-CODE			180									
TEMP =	200	C HP FR	60	C HP TO	90									
CT HZ FROM	30	CT HZ TO	60											
HTR-VOLTS	N/A	HTR-AMPS	N/A	HTR-WATTS		N/A	MAX. SPACE HEATER TEMP.			N/A	VT HZ FROM	O	VT HZ TO	60

AC Induction Motor Performance Data

Record # 93265

Typical performance - not guaranteed values

Winding: 10WGZ479-R001			Type: 1060M		Enclosure: TEFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		30	Full Load Torque		88.65 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		28	Breakdown Torque		267 LB-FT		
R.P.M.		1770	Pull-up Torque		120 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		146 LB-FT	
NEMA Design Code		B	KVA Code	G	Starting Current		174 A
Service Factor (S.F.)		1.15	No-load Current		10.53 A		
NEMA Nom. Eff.		93.6	Power Factor	84	Line-line Res. @ 25°C		0.379 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		63°C	
S.F. Amps				Temp. Rise @ S.F. Load		77°C	
				Locked-rotor Power Factor		30.6	
				Rotor inertia		4.77 lb-ft²	

Load Characteristics 575 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	49	72	81	84	86	85	83
Efficiency	91	94	94.3	93.6	93.6	91.9	93.6
Speed	1793	1786	1779	1772	1763	1753	1770
Line amperes	12.39	16.69	22.06	28.33	35.06	42.67	33.3


ABB Motors and Mechanical Inc.


WINDING # 10WGZ479

Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 1770 RPM 575 V 1060M

TORQUES (LB-FT): PO=267 PU=120 LR=146 LRA=174





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1