

ABB BALDOR RELIANCE III

Customer information packet

CECR9254T

25HP, 1770RPM, 3PH, 60HZ, 284T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	284TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	UR CCSA US NEMA_PREMIUM NEMA PREMIUM CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	31.000 A @ 460.0 V 62.000 A @ 230.0 V 68.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	J
Type	AC
Mech. spec.	10K455
Base	
Status	PRD/A
Elec. spec.	10WGZ352
Layout	10LYK455
Eff. date	10-08-2025
CD Diagram	CD0180
Poles	04
Leads	9#10
Proprietary	False
Created date	02-21-2019

Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	31.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1072M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	28.00 IN
Power Factor	81
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3293																
CAT.NO.	CECR9254T			P/N						ENCLOSURE		TEFC				
SPEC.	10K455Z352G1		CC	010A	FRAME		284TC		S/N							
HP	25		CLASS		F	HZ	60	DES	A							
RPM	1770		RPM MAX		2700		PH	3	KVA-CODE		G					
VOLT	230/460					I.P.		55								
AMP	62/31			SER.F.		1.25		PF	81	ODE BRG		6311		DE BRG	6312	
RATING	40C AMB-CONT			NEMA-NOM-EFF				93.6		GREASE		POLYREX EM				
HTR-VOLTS	HTR-AMPS		HTR-WATTS					INV.TYPE								
	SFA 76/38															
				C HP FR		60		C HP TO		90						
				CT HZ FROM			6		CT HZ TO			60				
				MOTOR WEIGHT				526		VT HZ FROM			6		VT HZ TO	60

AC Induction Motor Performance Data

Record # 50324

Typical performance - not guaranteed values

Winding: 10WGZ352-R001			Type: 1072M		Enclosure: TEFC			
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		25		Full Load Torque		73.8 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		62/31		Breakdown Torque		208 LB-FT		
R.P.M.		1770		Pull-up Torque		133 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		187 LB-FT		
NEMA Design Code		A	KVA Code	G		Starting Current	188 A	
Service Factor (S.F.)		1.25		No-load Current		12.5 A		
NEMA Nom. Eff.		93.6	Power Factor	81		Line-line Res. @ 25°C		0.26065 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		51°C		
S.F. Amps		76/38		Temp. Rise @ S.F. Load		70°C		
				Locked-rotor Power Factor		34.7		

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	77	81	83	83	83
Efficiency	90	93.5	94.1	93.8	93.2	92.3	93.2
Speed	1793.1	1787.4	1781.1	1773.7	1766.2	1757.2	1766
Line amperes	14.3	18.5	24.1	30.6	37.7	45.7	37.7


ABB Motors and Mechanical Inc.


WINDING # 10WGZ352

Typical performance - not guaranteed values.




25 HP 3 PH 60 HZ 1770 RPM 460 V 1072M

TORQUES (LB-FT): PO=208 PU=133 LR=187 LRA=188





CD0180


LOW VOLTAGE
(2D)

HIGH VOLTAGE
(1D)


NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1