

ABB BALDOR RELIANCE III

Customer information packet

CEM2513T-G

15HP, 1765RPM, 3PH, 60HZ, 254TC, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	254TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	36.000 A @ 230.0 V 18.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	18.0 a

Part Detail

Revision	P
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	39WGY375
Layout	39LYE477
Eff. date	08-13-2025
CD Diagram	CD0180
Poles	04
Leads	9#12
Proprietary	False
Created date	03-03-2020

Insulation Class	H
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3948M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	23.19 IN
Power Factor	85
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA											
CAT.NO.	CEM2513T-G										
SPEC.	39-0000817										
HP	15										
VOLTS	230/460										
AMPS	36.4/18.2										
RPM	1770										
FRAME	254TC		HZ		60		PH		3		
SF	1.15	CODE		J	DES		A	CLASS		H	
NEMA NOM. EFF	93	PF		83							
RATING	40C AMB-CONT										
CC	010A										
ENCL	OPSB	SN									
DE	6309		ODE		6208						
VPWM INVERTER READY											
CT30-60(2:1) VT3-60(20:1)											
USABLE AT	50HZ 15HP 190/380V 44/22A										SF1.0

AC Induction Motor Performance Data

Record # 67094

Typical performance - not guaranteed values

Winding: 39WGY375-R002			Type: 3948M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		15	Full Load Torque		44.53 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		36/18	Breakdown Torque		141 LB-FT		
R.P.M.		1765	Pull-up Torque		60.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		77.2 LB-FT	
NEMA Design Code		A	KVA Code	G	Starting Current		117 A
Service Factor (S.F.)		1.15	No-load Current		6.37 A		
NEMA Nom. Eff.		93	Power Factor	85	Line-line Res. @ 25°C		0.62591 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		26°C
S.F. Amps					Temp. Rise @ S.F. Load		32°C
					Locked-rotor Power Factor		32.8

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	51	73	81	85	87	87	86
Efficiency	89.9	93.1	93.5	93	92.3	91.2	92.6
Speed	1792	1784.7	1776.9	1768	1759.3	1748.7	1763
Line amperes	7.67	10.4	13.8	17.7	21.8	26.5	20.2


ABB Motors and Mechanical Inc.


WINDING # 39WGY375

Typical performance - not guaranteed values.




15 HP 3 PH 60 HZ 1765 RPM 460 V 3948M

TORQUES (LB-FT): PO=141 PU=60.4 LR=77.2 LRA=117





CD0180


LOW VOLTAGE
(2D)

HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1

CD0180