ABB BALDOR RELIANCE

Customer information packet

CEM2513T

15HP, 1765RPM, 3PH, 60HZ, 254TC, 3948M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 1:16:20 PM

Specifications

Enclosure	OPSB
Frame	254TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
	NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	36.400 A @ 230.0 V
	39.000 A @ 208.0 V
	18.200 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	Q
Type	AC
Mech. spec.	39D102
Base	
Status	PRD/A
Elec. spec.	39WGY375
Layout	39LYD102
Eff. date	12-12-2025
CD Diagram	CD0180
Poles	04
Leads	9#12
Proprietary	False
Created date	10-02-2017

Heater Indicator	No Heater
High Voltage Full Load Amps	18.2 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3948M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	23.19 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3554LUA												
CAT.NO.	CEM2513T			**P/N**						**ENCL**	OPSB	
SPEC.	39D102Y375G1	**CC**	010A		**FRAME**	254TC		**SER.NO.**				
HP	15		**CLASS**	F	**HZ**	60						
RPM	1770		**PH**	3	**DES**	A						
VOLTS	230/460			**CODE**	J		**ODE BRG**	6208	**DE BRG**	6309		
AMPS	36.4/18.2											
RATING	40C AMB-CONT			**NEMA-NOM-EFF**	93			**GREASE**	POLYREX EM			
PF	83	**SER.F.**	1.15			**CT30-60(2:1) VT3-60(20:1)**						
USABLE AT	50HZ 15HP 190/380V 44/22A				SF 1.0							
HTR-VOLTS	**HTR-AMPS**			**MAX. SPACE HEATER TEMP.**								

AC Induction Motor Performance Data
Record # 93498
Typical performance - not guaranteed values

Winding: 39WGY375-R001	**Type:** 3948M	**Enclosure:** OPSB

Nameplate Data			
Rated Output (HP)			15
Volts			230/460
Full Load Amps			36/18
R.P.M.			1770
Hz	60	**Phase**	3
NEMA Design Code	A	**KVA Code**	J
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	93	**Power Factor**	83
Rating - Duty			40C AMB-CONT
S.F. Amps			

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	44.57 LB-FT
Start Configuration	direct on line
Breakdown Torque	171 LB-FT
Pull-up Torque	79.1 LB-FT
Locked-rotor Torque	100 LB-FT
Starting Current	137 A
No-load Current	7.62 A
Line-line Res. @ 25ºC	0.5794 Ω
Temp. Rise @ Rated Load	29°C
Temp. Rise @ S.F. Load	35°C
Locked-rotor Power Factor	32.8

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	45	68	78	83	86	87	85
Efficiency	88.6	92.6	93.3	93.1	92.5	91.7	92.7
Speed	1794.2	1788	1781.2	1773.7	1766.3	1758.2	1769
Line amperes	8.77	11.2	14.5	18.2	22.1	26.4	20.5


ABB Motors and Mechanical Inc.

WINDING # 39WGY375

15 HP 3 PH 60 HZ 1770 RPM 460 V 3948M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=171 PU=79.1 LR=100 LRA=137




11/13/2026 ACPERF, record # 93498

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1