

ABB BALDOR RELIANCE III

Customer information packet

CEDM3559T

3HP, 3450RPM, 3PH, 60HZ, 145TC, 3532M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	143TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	7.900 A @ 208.0 V 7.200 A @ 230.0 V 3.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	H
Type	AC
Mech. spec.	35E4328
Base	
Status	PRD/A
Elec. spec.	35WGQ060
Layout	35LYE4328
Eff. date	12-18-2025
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	05-11-2016

Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.6 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.23 IN
Power Factor	92
Product Family	Dirty Duty Plus
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed

Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3504											
CAT NO	CEDM3559T										
SPEC.	35E4328Q060G1					ENCL	TEFC				
FRAME	143TC	HP	3								
VOLTS	230/460										
FLA	7.2/3.6			I.P.		56					
RPM	3450	RPM MAX			5400						
HZ	60	PH	3	CLASS		F					
SER.F.	1.15	DES	B	CC	010A						
NEMA-NOM-EFF	86.5										
RATING	40C AMB-CONT										
DE BRG	6205	ODE BRG			6203						
GREASE	POLYREX EM										
INV.TYPE		C HP FR		60	C HP TO		90				
CT HZ FROM	6	CT HZ TO		60	VT HZ FROM		6	VT HZ TO		60	
SER.NO	50C AT 1.0 SF										

AC Induction Motor Performance Data

Record # 55733

Typical performance - not guaranteed values

Winding: 35WGQ060-R032			Type: 3532M		Enclosure: TEFC			
Nameplate Data			460 V, 60 Hz: High Voltage Connection					
Rated Output (HP)		3	Full Load Torque		4.5 LB-FT			
Volts		230/460	Start Configuration		direct on line			
Full Load Amps		7.2/3.6	Breakdown Torque		18 LB-FT			
R.P.M.		3450	Pull-up Torque		11 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		16 LB-FT		
NEMA Design Code		B	KVA Code	L	Starting Current		33 A	
Service Factor (S.F.)		1.15		No-load Current		1.2 A		
NEMA Nom. Eff.		86.5	Power Factor		92	Line-line Res. @ 25°C		4.72 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		61°C		
S.F. Amps				Temp. Rise @ S.F. Load		76°C		

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	62	81	88	92	93	94	93
Efficiency	83.7	87.9	88.2	87.2	85.6	83.5	86.2
Speed	3562	3531	3498	3462	3421	3375	3437
Line amperes	1.5	2.1	2.8	3.6	4.5	5.4	4.1

ABB Motors and Mechanical Inc.

WINDING # 35WGQ060

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 3450 RPM 460 V 3532M

TORQUES (LB-FT): PO=18 PU=11 LR=16 LRA=33





