ABB BALDOR RELIANCE

Customer information packet

CEDM3611T

3HP, 1764RPM, 3PH, 60HZ, 182TC, 3630M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 3:23:07 PM

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM
	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	4.160 A @ 460.0 V
	8.320 A @ 230.0 V
	8.800 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	A
Type	AC
Mech. spec.	36Q736
Base	
Status	PRD/A
Elec. spec.	36WGZ650
Layout	36LYQ736
Eff. date	04-16-2026
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	11-05-2025

High Voltage Full Load Amps	4.2 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3630M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	16.60 IN
Power Factor	74
Product Family	Dirty Duty Plus
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1764 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3504									
CAT NO	CEDM3611T								
SPEC.	36Q736Z650			**ENCL**	TEFC				
FRAME	182TC	**HP**	3						
VOLTS	230/460								
FLA	8.4/4.2			**I.P.**	56				
RPM	1765	**RPM MAX**							
HZ	60	**PH**	3	**CLASS**	F				
SER.F.	1.15	**DES**	B	**CC**	010A				
NEMA-NOM-EFF	89.5								
RATING	40C AMB-CONT								
DE BRG	6206	**ODE BRG**	6205						
GREASE	POLYREX EM								
INV.TYPE		**C HP FR**	60	**C HP TO**	90				
CT HZ FROM	6	**CT HZ TO**	60	**VT HZ FROM**	6	**VT HZ TO**	60		
SER.NO									
	50C AT 1.0SF								

AC Induction Motor Performance Data
Record # 115759
Typical performance - not guaranteed values

Winding: 36WGZ650-R001	**Type:** 3630M	**Enclosure:** TEFC

Nameplate Data			
Rated Output (HP)			3
Volts			230/460
Full Load Amps			8.4/4.2
R.P.M.			1765
Hz	60	**Phase**	3
NEMA Design Code	B	**KVA Code**	K
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	89.5	**Power Factor**	74
Rating - Duty			40C AMB-CONT
S.F. Amps			9.4/4.7

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	8.942 LB-FT
Start Configuration	direct on line
Breakdown Torque	38.2 LB-FT
Pull-up Torque	19.1 LB-FT
Locked-rotor Torque	22.4 LB-FT
Starting Current	32.2 A
No-load Current	2.38 A
Line-line Res. @ 25ºC	3.8717 Ω
Temp. Rise @ Rated Load	46°C
Temp. Rise @ S.F. Load	56°C
Locked-rotor Power Factor	42.6
Rotor inertia	0.279 lb-ft²

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	33	54	67	74	79	81	77
Efficiency	82.2	88.4	89.8	89.8	89	87.9	89.3
Speed	1790.7	1781.4	1771.4	1761.2	1749.9	1738.7	1754
Line amperes	2.54	2.94	3.51	4.2	4.99	5.87	4.67


ABB Motors and Mechanical Inc.


WINDING # 36WGZ650

3 HP 3 PH 60 HZ 1765 RPM 460 V 3630M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=38.2 PU=19.1 LR=22.4 LRA=32.2




36LYQ736
614-623 = 15.22
624-634 = 16.60
635-646 = 18.10
4.64
(635-646 ONLY)
2.75
.25
.25 KEY
1.75 LONG
2.62
8.86
Ø8.50
NAMEPLATE
1.1250
1.1245
Ø 8.500
8.497
6 HOLES
.41 DIA.
4.50
.50
5.50
3.50
6.50
4 HOLES
W/3 PLUGGED
(EA. END)
DRAIN FITTING
(EA. END)
Ø7.86
6.65
2.24
45°
45°
8.43
4.50 +.00 -.06
4 HOLES
.50-13 TAP
.75 DEEP ON
Ø7.25 B.C.
LEAD HOLE
.75 N.P.T.
3.75
3.75
5.44
4.31
8.63
OPPOSITE END DETAIL
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD ".75 DEEP ON" TO T-BOLT HOLES TO DWG
REV: B
VERSION: 02
REVISED: 11:23:45 09/12/2024
TDR: 000001240863
MODEL NO. 36LYQ736
REF: -
BY: USCHHOL5
B
BALDOR - RELIANCE®
STD HORZ 182-4TC TEFC 36M DDP
36LYQ736

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS