

ABB BALDOR RELIANCE III

Customer information packet

CEFWWDM3550

1.5HP, 3500RPM, 3PH, 60HZ, 56C, 3528M, TEFC, F1

Class -

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	RG
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.000 A @ 230.0 V 4.000 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	J
Type	AC
Mech. spec.	35E1679
Base	
Status	INA/A
Elec. spec.	35WGR445
Layout	35LYE1679
Eff. date	04-09-2016
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	11-19-2012

High Voltage Full Load Amps	2.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	13.35 IN
Power Factor	87
Product Family	Super White Washdown
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP1669L											
CAT.NO.	CEFWWDM3550										
SPEC.	35E1679R445G1										
HP	1.5										
VOLTS	208-230/460										
AMP	4/2										
RPM	3500										
FRAME	56C		HZ	60				PH	3		
SER.F.	1.15	CODE	N	DES	B	CLASS		F			
NEMA-NOM-EFF	85.5	PF	87								
RATING	40C AMB-CONT										
CC	010A										
DE	6205		ODE	6205							
ENCL	TEFC	SN									
BLANK											

AC Induction Motor Performance Data

Record # 20327

Typical performance - not guaranteed values

Winding: 35WGR445-R006			Type: 3528M		Enclosure: TENV			
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1.5		Full Load Torque		2.3 LB-FT		
Volts		208-230/460		Start Configuration		direct on line		
Full Load Amps		4/2		Breakdown Torque		12 LB-FT		
R.P.M.		3500		Pull-up Torque		8.2 LB-FT		
Hz		60	Phase	3	Locked-rotor Torque		11 LB-FT	
NEMA Design Code		B	KVA Code		N		Starting Current	23.5 A
Service Factor (S.F.)		1.15		No-load Current		0.9 A		
NEMA Nom. Eff.		85.5	Power Factor		87		Line-line Res. @ 25°C	6.95 Ω
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		73°C
S.F. Amps						Temp. Rise @ S.F. Load		84°C
						Locked-rotor Power Factor		48.4

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	51	71	81	87	90	91	89
Efficiency	73.8	82.5	85.2	86.1	86	85.4	86
Speed	3568	3544	3519	3493	3466	3434	3477
Line amperes	1.1	1.3	1.6	1.9	2.3	2.8	2.14

ABB Motors and Mechanical Inc.

WINDING # 35WGR445

Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 3500 RPM 460 V 3528M

TORQUES (LB-FT) : PO=12 PU=8.2 LR=11 LRA=23.5





