ABB BALDOR RELIANCE

Customer information packet

CEM3157T-G

2HP, 1765RPM, 3PH, 60HZ, 145TC, 3528M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 9:39:01 PM

Specifications

Enclosure	OPSB
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UR
	NEMA_PREMIUM
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.800 A @ 460.0 V
	5.600 A @ 208.0 V
	5.600 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WGG073
Layout	35LY-000-271
Eff. date	01-02-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	10-28-2021

High Voltage Full Load Amps	2.8 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.12 IN
Power Factor	81
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	CEM3157T-G								
SPEC.	35-0000-1357								
HP	2								
VOLTS	230/460								
AMPS	5.6/2.8								
RPM	1760								
FRAME	145TC	**HZ**	60			**PH**	3		
SF	1.15	**CODE**	K	**DES**	B	**CLASS**	H		
NEMA NOM. EFF	86.5	**PF**	77						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	**SN**							
DE	6205		**ODE**	6203					
VPWM INVERTER READY		SFA 6.3/3.15							
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 2HP 190/380V 6.3/3.15A								SF1.0

AC Induction Motor Performance Data
Record # 87421
Typical performance - not guaranteed values

Winding: 35WGG073-R010	**Type:** 3528M	**Enclosure:** OPEN

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			2	**Full Load Torque**	5.99 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			5.6/2.8	**Breakdown Torque**	20.5 LB-FT
R.P.M.			1760	**Pull-up Torque**	13.8 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	15 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	22.5 A
Service Factor (S.F.)			1.15	**No-load Current**	1.62 A
NEMA Nom. Eff.	86.5	**Power Factor**	74	**Line-line Res. @ 25ºC**	9.54 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C
S.F. Amps				**Temp. Rise @ S.F. Load**	77°C
				Locked-rotor Power Factor	57.9
				Rotor inertia	0.202 lb-ft²

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	35	55	68	76	81	84	83
Efficiency	78.2	85.3	86.8	86.5	85.4	83.6	86.3
Speed	1791	1782	1771	1760	1748	1734	1758
Line amperes	1.71	1.97	2.34	2.82	3.36	3.97	3.02


ABB Motors and Mechanical Inc.

WINDING # 35WGG073


2 HP 3 PH 60 HZ 1760 RPM 460 V 3528M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=20.5 PU=13.8 LR=15 LRA=22.5




11/13/2026 ACPERF, record # 87421


35LY-000-271
510-524 = 11.62
525-528 = 12.13
529-535 = 13.00
536-546 = 14.38
2.60
2.13
.12
.13
.19 KEY
1.38 LONG
NAMEPLATE
Ø 4.500
4.495
.8750
.8745
6.49
6 HOLES
Ø .38
4.00
.50
5.00
2.75
5.94
Ø 6.68
5.62
45°
45°
6.78
3.50
3.44
4 HOLES
.38-16 TAP
Ø 5.88 B.C.
LEAD HOLE
Ø 1.09
2.75
2.75
4.56
3.25
6.50
SHAFT
GROUND
6205
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD TO SWD DRAWING
REV: A
VERSION: 01
REVISED: 10:31:04 05/10/2024
TDR: 000001231935
MODEL NO. 35LY-000-271
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HOR 143-5TC OPSB 35M W/AEGIS INT SHAFT GROUND & "W" BASE
35LY-000-271

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS