ABB BALDOR RELIANCE

Customer information packet

CEM2551T-G

75HP, 1775RPM, 3PH, 60HZ, 365TC, OPSB, F1

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 6:46:56 AM

Specifications

Enclosure	OPSB
Frame	365TC
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	75.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	170.000 A @ 230.0 V
	85.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	85.0 a
Insulation Class	H
Inverter Code	Inverter Ready

Part Detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	44WGW013
Layout	44LY-000-014
Eff. date	11-19-2024
CD Diagram	CD0180
Poles	04
Leads	9#6
Proprietary	False
Created date	08-21-2019

IP Rating	NONE
KVA Code	F
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4462M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.72 IN
Power Factor	85
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3554LUA												
CAT.NO.	CEM2551T-G			**P/N**						**ENCL**	OPSB	
SPEC.	44-0000-0028	**CC**	010A		**FRAME**	365TC		**SER.NO.**				
HP	75		**CLASS**	H	**HZ**	60						
RPM	1775		**PH**	3	**DES**	B						
VOLTS	230/460			**CODE**	F		**ODE BRG**	6312	**DE BRG**	6313		
AMPS	170/85											
RATING	40C AMB-CONT			**NEMA-NOM-EFF**	95		**GREASE**	POLYREX EM				
PF	85	**SER.F.**	1.15		**CT30-60(2:1) VT3-60(20:1)**							
USABLE AT	50HZ 75HP 190/380V 204/102A			SF1.0								
HTR-VOLTS	**HTR-AMPS**		**MAX. SPACE HEATER TEMP.**									

AC Induction Motor Performance Data
Record # 31660
Typical performance - not guaranteed values

Winding: 44WGW013-R002	**Type:** 4462M	**Enclosure:** OPEN

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			75	**Full Load Torque**	222 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			170/85	**Breakdown Torque**	610 LB-FT
R.P.M.			1775	**Pull-up Torque**	235 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	327 LB-FT
NEMA Design Code	B	**KVA Code**	F	**Starting Current**	507 A
Service Factor (S.F.)			1.15	**No-load Current**	26.2 A
NEMA Nom. Eff.	95	**Power Factor**	85	**Line-line Res. @ 25ºC**	0.0799 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	30°C
S.F. Amps				**Temp. Rise @ S.F. Load**	37°C
				Locked-rotor Power Factor	26.3
				Rotor inertia	11.7 LB-FT2

Load Characteristics 460 V, 60 Hz, 75 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	56	77	84	86	87	87	86
Efficiency	93.6	95.6	95.4	95.3	94.6	93.9	94.7
Speed	1794	1788	1782	1776	1769	1761	1776
Line amperes	33.9	48	66.1	85.4	106	128	100


ABB Motors and Mechanical Inc.


WINDING # 44WGW013

75 HP 3 PH 60 HZ 1775 RPM 460 V 4462M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=610 PU=235 LR=327 LRA=507





44LY-000-014
(4436-4456) = 31.72
(4458-4486) = 33.72
7.76
5.62
.27
GREASER & PIPE PLUG
(EA. END)
.62 KEY
4.25 LONG
13.53
Ø12.500
12.497
Ø2.375
2.374
8 HOLES
Ø.65
11.25
11.25
1.11
12.25
5.87
14.50
BP5315
PU. END DETAIL
Ø16.79
16.57
8.40
1 LIFTING LUG
(EA. SIDE)
DIAGONALLY
SPACED
17.52
9.13 +.00 -.06
LEAD
HOLE
Ø3.62
.78
7.00
7.00
12.13
8.50
17.00
8 HOLES
.62-11 TAP ON
Ø11.00 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADDED THE C-FACE MOUNTING HOLES CALL OUT
REV: C
VERSION: 03
REVISED: 10:00:26 02/23/2026
TDR: 000001272470
MODEL NO. 44LY-000-014
REF: -
BY: ENSHAB0
B
BALDOR - RELIANCE®
HOR OPSB 364-5TC W/INT SH GND
44LY-000-014

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1