

ABB BALDOR RELIANCE III

Customer information packet

CEM3305T

3HP, 1165RPM, 3PH, 60HZ, 213TC, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	213TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.500 A @ 460.0 V 9.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	4.5 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGR333
Layout	37LYB102
Eff. date	01-02-2026
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	02-24-2020

IP Rating	NONE
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3734M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	17.07 IN
Power Factor	71
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1259L											
CAT.NO.	CEM3305T										
SPEC.	37-0000-0204										
HP	3										
VOLTS	230/460										
AMP	9/4.5										
RPM	1165										
FRAME	213TC		HZ	60				PH	3		
SER.F.	1.15		CODE	K	DES	B	CL	F			
NEMA-NOM-EFF	88.5		PF	71							
RATING	40C AMB-CONT										
CC	010A										
DE	6307		ODE	6206							
ENCL	OPSB		SN								

AC Induction Motor Performance Data

Record # 49691

Typical performance - not guaranteed values

Winding: 37WGR333-R005			Type: 3734M		Enclosure: OPSB	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		3	Full Load Torque		13.59 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		9/4.5	Breakdown Torque		46.48 LB-FT	
R.P.M.		1165	Pull-up Torque		21.64 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque	35.84 LB-FT	
NEMA Design Code	B	KVA Code	K	Starting Current	31.11 A	
Service Factor (S.F.)		1.15	No-load Current		2.38 A	
NEMA Nom. Eff.	88.5	Power Factor	71	Line-line Res. @ 25°C	3.48 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		20°C	
S.F. Amps			Temp. Rise @ S.F. Load		24°C	
			Locked-rotor Power Factor		25.2	
			Rotor inertia		0.846 LB-FT2	

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	34	53	64	71	74	76	73
Efficiency	82.9	88.4	89.4	88.9	88	86.1	88.4
Speed	1192	1185	1177	1168	1158	1147	1161
Line amperes	2.57	3.06	3.73	4.49	5.41	6.45	5.04


ABB Motors and Mechanical Inc.


WINDING # 37WGR333

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 1165 RPM 460 V 3734M

TORQUES (LB-FT) : PO=46.48 PU=21.64 LR=35.84 LRA=31.11





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005