ABB BALDOR RELIANCE

Customer information packet

CEM3312T-G

10HP, 3475RPM, 3PH, 60HZ, 213TC, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/14/2026 10:13:23 PM

Specifications

Enclosure	OPSB
Frame	213TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	24.000 A @ 230.0 V
	12.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	12.0 a

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGS633
Layout	37LYK447
Eff. date	06-11-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	03-08-2020

Insulation Class	H
Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	17.06 IN
Power Factor	86
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	3475 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	CEM3312T-G								
SPEC.	37-0000815								
HP	10								
VOLTS	230/460								
AMPS	24/12								
RPM	3475								
FRAME	213TC	**HZ**	60			**PH**	3		
SF	1.15	**CODE**	G	**DES**	B	**CLASS**	H		
NEMA NOM. EFF	89.5	**PF**	86						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	**SN**							
DE	6307	**ODE**	6206						
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 10HP 190/380V 28.4/14.2A								SF1.0

AC Induction Motor Performance Data
Record # 53395
Typical performance - not guaranteed values

Winding: 37WGS633-R010	**Type:** 3728M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	15 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			24/12	**Breakdown Torque**	51.1 LB-FT
R.P.M.			3475	**Pull-up Torque**	25.6 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	30 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	79 A
Service Factor (S.F.)			1.15	**No-load Current**	4.54 A
NEMA Nom. Eff.	89.5	**Power Factor**	86	**Line-line Res. @ 25ºC**	0.98748 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	29°C
S.F. Amps				**Temp. Rise @ S.F. Load**	35°C
				Locked-rotor Power Factor	35
				Rotor inertia	0.255 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	52	74	82	86	88	88	87
Efficiency	84.2	89.7	90.6	90.2	89.3	87.9	89.7
Speed	3578.4	3552.7	3525.5	3493.1	3458.3	3422.6	3472
Line amperes	5.31	7.03	9.39	12	14.8	18	13.7


ABB Motors and Mechanical Inc.


WINDING # 37WGS633

10 HP 3 PH 60 HZ 3475 RPM 460 V 3728M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=51.1 PU=25.6 LR=30 LRA=79




37LYK447
(717-735) = 17.07
(736-744) = 18.19
(745-750) = 18.94
(751-756) = 19.69
3.44
3.12
.26
GREASE FITTING (EA. END)
.31 KEY 2.25 LONG
9.06
8.500
8.497
Ø 1.3750
1.3745
6 HOLES Ø .41
5.50
4.24
7.00
.50
8.00
Ø9.57
7.88
4.78
45°
45°
LIFTING LUG (1 EA. END)
10.04
5.25 +.00 -.06
4 HOLES .50-13 TAP ON Ø7.25 B.C.
LEAD HOLE Ø 1.38
4.25
4.25
6.72
4.75
9.50
INTERNAL SHAFT GROUND
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD DRAWING TO SOLIDWORKS
REV: A
VERSION: 01
REVISED: 03:31:55 06/14/2022
TDR: 000001192277
MODEL NO. 37LYK447
REF: -
BY: ENALEM0
B
BALDOR
HOR 213-5TC OPSB M W/AEGIS INT SHAFT GND
37LYK447

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS