

ABB BALDOR RELIANCE III

Customer information packet

CEM3312T-G

10HP, 3475RPM, 3PH, 60HZ, 213TC, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	213TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	24.000 A @ 230.0 V 12.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	12.0 a

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGS633
Layout	37LYK447
Eff. date	06-11-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	03-08-2020

Insulation Class	H
Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	17.06 IN
Power Factor	86
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	3475 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	CEM3312T-G								
SPEC.	37-0000815								
HP	10								
VOLTS	230/460								
AMPS	24/12								
RPM	3475								
FRAME	213TC		HZ	60		PH	3		
SF	1.15	CODE	G	DES	B	CLASS	H		
NEMA NOM. EFF	89.5	PF	86						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	SN							
DE	6307		ODE	6206					
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 10HP 190/380V 28.4/14.2A						SF1.0		

AC Induction Motor Performance Data

Record # 53395

Typical performance - not guaranteed values

Winding: 37WGS633-R010			Type: 3728M		Enclosure: OPSB	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		10	Full Load Torque		15 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		24/12	Breakdown Torque		51.1 LB-FT	
R.P.M.		3475	Pull-up Torque		25.6 LB-FT	
Hz		60	Phase		3	
NEMA Design Code		B	KVA Code		G	
Service Factor (S.F.)		1.15	No-load Current		4.54 A	
NEMA Nom. Eff.		89.5	Power Factor		86	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		29°C
S.F. Amps				Temp. Rise @ S.F. Load		35°C
				Locked-rotor Power Factor		35
				Rotor inertia		0.255 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	52	74	82	86	88	88	87
Efficiency	84.2	89.7	90.6	90.2	89.3	87.9	89.7
Speed	3578.4	3552.7	3525.5	3493.1	3458.3	3422.6	3472
Line amperes	5.31	7.03	9.39	12	14.8	18	13.7

ABB Motors and Mechanical Inc.

WINDING # 37WGS633

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 3475 RPM 460 V 3728M

TORQUES (LB-FT) : PO=51.1 PU=25.6 LR=30 LRA=79





