ABB BALDOR RELIANCE

Customer information packet

CEM3607T-G

1.5HP, 1165RPM, 3PH, 60HZ, 182TC, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 8:17:37 PM

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.800 A @ 230.0 V
	2.400 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	87.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	2.4 a

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGS916
Layout	36LYN147
Eff. date	01-02-2026
CD Diagram	CD0005
Poles	06
Leads	9#16
Proprietary	False
Created date	12-16-2019

Insulation Class	H
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3632M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	16.55 IN
Power Factor	67
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA											
CAT.NO.	CEM3607T-G										
SPEC	36-0000-0251										
HP	1.5										
VOLTS	230/460										
AMPS	4.8/2.4										
RPM	1165										
FRAME	182TC	**HZ**	60	**PH**	3						
SF	1.15	**CODE**	K	**DES**	B	**CLASS**	H				
NEMA NOM. EFF	87.5	**PF**	67								
RATING	40C AMB-CONT										
CC	010A										
ENCL	TEFC	**SER**									
DE	6206	**ODE**	6205								
VPWM INVERTER READY											
CT6-60H(10:1)VT3-60H(20:1											
	50HZ 1.5HP 190/380V 4.8/2.4A										SF1.0

AC Induction Motor Performance Data
Record # 38401
Typical performance - not guaranteed values

Winding: 36WGS916-R002	**Type:** 3632M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	6.86 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			4.8/2.4	**Breakdown Torque**	23.8 LB-FT
R.P.M.			1165	**Pull-up Torque**	12.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	15.3 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	15.8 A
Service Factor (S.F.)			1.15	**No-load Current**	1.47 A
NEMA Nom. Eff.	87.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	7.3716 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	34°C
S.F. Amps				**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	30
				Rotor inertia	0.301 LB-FT2

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	30	48	59	67	71	74	69
Efficiency	79.1	86	87.5	87.5	86.5	85.2	86.9
Speed	1192.2	1184.8	1176.8	1168.1	1158.2	1147.5	1162
Line amperes	1.57	1.77	2.07	2.43	2.88	3.36	2.7


ABB Motors and Mechanical Inc.


WINDING # 36WGS916

1.5 HP 3 PH 60 HZ 1165 RPM 460 V 3632M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=23.8 PU=12.5 LR=15.3 LRA=15.8




36LYN147
(614-623) = 15.18
(624-634) = 16.55
(635-646) = 18.04
(635-646 ONLY)
4.27
2.62
.25
2.75
.25 KEY
1.75 LONG
GREASE
FITTING
(EA. END)
Ø8.60
NAMEPLATE
Ø8.500
8.497
8.85
1.1250
1.1245
6 HOLES
.41 DIA.
4.50
.50
5.50
3.50
6.50
Ø7.86
6.87
45°
45°
2.22
8.43
4.50 +.00 -.06
LEAD HOLE
1.09 DIA.
3.75
3.75
5.75
4.31
8.63
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD TO SWD DRAWING
REV: B
VERSION: 02
REVISED: 03:33:29 05/02/2024
TDR: 000001230132
MODEL NO. 36LYN147
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HORZ FACE MTD 182-4TC TEFC 36M W/INT SH GND (AEGIS)
36LYN147

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS