ABB BALDOR RELIANCE

Customer information packet

CEM3764T

3HP, 1165RPM, 3PH, 60HZ, 213TC, 0736M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 6:10:27 AM

Specifications

Enclosure	TEFC
Frame	213TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
	NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.000 A @ 208.0 V
	9.000 A @ 230.0 V
	4.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	U
Type	AC
Mech. spec.	07H058
Base	
Status	PRD/A
Elec. spec.	07WGX970
Layout	07LYH058
Eff. date	08-10-2026
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	06-14-2010

Heater Indicator	No Heater
High Voltage Full Load Amps	4.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.20 IN
Power Factor	71
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA										
CAT.NO.	CEM3764T									
SPEC	07H058X970G1									
HP	3									
VOLTS	230/460									
AMPS	9/4.5									
RPM	1165									
FRAME	213TC	**HZ**	60		**PH**	3				
SF	1.15	**CODE**	K	**DES**	B	**CLASS**	F			
NEMA NOM. EFF	89.5	**PF**	71							
RATING	40C AMB-CONT									
CC	010A									
ENCL	TEFC	**SER**								
DE	6307	**ODE**	6206							
VPWM INVERTER READY	SFA 9.8/4.9									
CT6-60H(10:1)VT3-60H(20:1										
	50Hz 3HP 190/380V 10.4/5.2A									SF1.0

AC Induction Motor Performance Data
Record # 53091
Typical performance - not guaranteed values

Winding: 07WGX970-R023	**Type:** 0736M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			3	**Full Load Torque**	13.61 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			9/4.5	**Breakdown Torque**	51.71 LB-FT
R.P.M.			1165	**Pull-up Torque**	25.77 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	31.08 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	32.19 A
Service Factor (S.F.)			1.15	**No-load Current**	2.26 A
NEMA Nom. Eff.	89.5	**Power Factor**	71	**Line-line Res. @ 25ºC**	3 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	34°C
S.F. Amps				**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	23.3
				Rotor inertia	0.895 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	35	54	65	72	75	76	73
Efficiency	82.8	88.3	89.7	89.6	89	87.3	89.4
Speed	1192	1184	1176	1166	1156	1143	1161
Line amperes	2.48	2.96	3.62	4.41	5.29	6.33	4.99


ABB Motors and Mechanical Inc.


WINDING # 07WGX970

3 HP 3 PH 60 HZ 1165 RPM 460 V 0736M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=51.71 PU=25.77 LR=31.08 LRA=32.19




07LYH058
(717-750) = 19.19
8.07
3.12
GREASE FITTING
(EA. END)
.26
.31 KEY
2.38 LONG
Ø10.28
8.500
8.497
9.06
Ø1.3750
1.3745
5.50
.56
5.50
4.50
7.00
8.13
8 HOLES
.41 DIA.
GREASE RELIEF
(EA. END)
11.50
9.37
6.00
45°
45°
2.04
4 HOLES
.50-13 TAP
Ø7.25 B.C.
10.99
5.25 +.00 -.06
LEAD HOLE
1.38 DIA.
4.25
4.25
7.48
4.92
9.83
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT FROM AUTOCAD TO SWD
REV: N
VERSION: 04
REVISED: 03:12:03 10/31/2023
TDR: 000001218972
MODEL NO. 07LYH058
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HORZ 213-5TC TEFC 307M SUPER-E
07LYH058

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS