

ABB BALDOR RELIANCE III

Customer information packet

CEM4102T-G

20HP, 1180RPM, 3PH, 60HZ, 286TC, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	286TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	54.000 A @ 230.0 V 27.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	27.0 a

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGY730
Layout	10LYJ646
Eff. date	06-27-2024
CD Diagram	CD0180
Poles	06
Leads	9#10
Proprietary	False
Created date	03-06-2020

Insulation Class	H
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1054M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	27.76 IN
Power Factor	77
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3443LUA											
CAT.NO.	CEM4102T-G			CUST. P/N				ENCL			TEFC
SPEC.	10-0000835	CC	010A	FRAME	286TC	SER.NO.					
HP	20		CLASS	H	HZ	60					
R.P.M.	1180		PH.	3	DES.	A					
VOLTS	230/460		CODE		H	ODE BRG		6309	DE BRG	6311	
AMPS	54/27										
RATING	40C AMB-CONT		NEMA NOM. EFF.			91.7	GREASE		POLYREX EM		
P.F.	77	SER.F.	1.15	CT6-60H(10:1)VT3-60H(20:1							
USABLE AT	50HZ 20HP 190/380V 62/31A			SF1.0							
VOLTS	AMPS	MAX. SPACE HEATER TEMP.									

AC Induction Motor Performance Data

Record # 53030

Typical performance - not guaranteed values

Winding: 10WGY730-R018				Type: 1054M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		20		Full Load Torque		90.1 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		54/27		Breakdown Torque		276 LB-FT		
R.P.M.		1180		Pull-up Torque		115 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		166 LB-FT		
NEMA Design Code		A	KVA Code	Starting Current		165 A		
Service Factor (S.F.)		1.15		No-load Current		13.1 A		
NEMA Nom. Eff.		91.7	Power Factor	77	Line-line Res. @ 25°C		0.425 Ω	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		65°C
S.F. Amps						Temp. Rise @ S.F. Load		79°C
						Locked-rotor Power Factor		32
						Rotor inertia		6.61 LB-FT ²

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	39	60	71	77	79	80	78
Efficiency	86.6	91.1	91.9	91.7	90.9	89.8	91.2
Speed	1194.6	1189.5	1184.1	1178.3	1171.4	1163.8	1174
Line amperes	14.3	17.5	21.9	26.9	32.7	39.3	30.4


ABB Motors and Mechanical Inc.

WINDING # 10WGY730

Typical performance - not guaranteed values.

20 HP 3 PH 60 HZ 1180 RPM 460 V 1054M

TORQUES (LB-FT): PO=276 PU=115 LR=166 LRA=165







CD0180



LOW VOLTAGE
(2D)



HIGH VOLTAGE
(1D)



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: —



BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1

CD0180