

ABB BALDOR RELIANCE III

Customer information packet

CEM3714T

10HP, 1768RPM, 3PH, 60HZ, 215TC, 3750M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.400 A @ 460.0 V 24.800 A @ 230.0 V 27.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.4 a

Part Detail

Revision	-
Type	AC
Mech. spec.	37G814
Base	
Status	PRD/A
Elec. spec.	37WGZ711
Layout	37LYG814
Eff. date	11-24-2025
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	11-05-2025

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3750M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	20.50 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1768 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	CEM3714T								
SPEC	37G814Z711								
HP	10								
VOLTS	230/460								
AMPS	24.8/12.4								
RPM	1768								
FRAME	215TC		HZ	60			PH	3	
SF	1.15		CODE	K	DES	A	CLASS	F	
NEMA NOM. EFF	91.7		PF	85					
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6307		ODE	6206					
VPWM INVERTER READY	SFA 28.2/14.1								
CT6-60H(10:1)VT3-60H(20:1									
	50HZ 10HP 190/380V 29.8/14.9A								
	SF1.0								

AC Induction Motor Performance Data

Record # 115760

Typical performance - not guaranteed values

Winding: 37WGZ711-R001			Type: 3750M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		10	Full Load Torque		29.79 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		24.8/12.4	Breakdown Torque		93.4 LB-FT		
R.P.M.		1768	Pull-up Torque		44.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		55.5 LB-FT	
NEMA Design Code		A	KVA Code	K	Starting Current		90.5 A
Service Factor (S.F.)		1.15	No-load Current		5.11 A		
NEMA Nom. Eff.		91.7	Power Factor	85	Line-line Res. @ 25°C		1.1801 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		77°C
S.F. Amps		28.2/14.1	Temp. Rise @ S.F. Load		108°C		
			Locked-rotor Power Factor		37.2		

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	68	78	82	85	85	84
Efficiency	89.9	92.6	92.6	91.8	90.5	88.9	91
Speed	1792.4	1785	1776.3	1767.2	1756.7	1745.2	1756
Line amperes	5.83	7.54	9.79	12.4	15.3	18.6	14.2


ABB Motors and Mechanical Inc.


WINDING # 37WGZ711

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1768 RPM 460 V 3750M

TORQUES (LB-FT): PO=93.4 PU=44.7 LR=55.5 LRA=90.5





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005