

# DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION  
CAST IRON CONSTRUCTION

FRAMES 364TSC-365TSC

COOLING: FAN COOLED

ENCLOSURE: TOTALLY ENCLOSED  
MOUNTING: FOOT



617428-017

D

C

B

A



D

C

B

A

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND INCLUDING 1.625 DIA AND .003 T.I.R. 1.625 DIA. TO 5 INCH DIA.

WEIGHT (LBS): 364TSC = 809  
365TSC = 849

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

|  |             |                              |                   |
|--|-------------|------------------------------|-------------------|
| REV. DESC: UPDATE DRAWING TO HAVE CORRECT "AH" |             |                              |                   |
| REV: D   | VERSION: 04 | REVISED: 01:59:50 10/05/2015 | TDR: 000000947176 |
| MODEL NO. 617428-017                           |             |                              | REF:              |
| BY: RAGJSS1                                    |             |                              | <b>B</b>          |

**BALDOR**

DIM SHEET 364-5TSC TEFC (611740-003-SH1)

617428-017

8

7

6

5

4

3

2

1